

676 Series Panel Mount Indicators





# **Application**

- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation
- ...and many more!

# **Certifications & Ratings**

• RoHS compliant

# Features & Benefits

- Low power consumption uses up to 90% less energy than
  an incandescent indicator
- No heat generated
- Long life, lasting up to 100K hours
- Colors include red, green, orange, blue, and white
- Front panel mounting
- LED can be recessed or protrude from housing

Mechanical Information:				
Mounting hole size:	0.244" (6.2mm)			
Max panel thickness:	0.138" (3.5mm)			
Mounting torque:	0.362 lbs/ft (5 kg/cm)			
Electrical Specifications:				
Operating voltage:	2 (red, orange) & 3.3 (green, blue) VDC (current limiting resistor required on both voltages)			
Operating temperature:	-22°F to +185°F (-30°C to +85°C)			
Storage temperature:	-40°F to +212°F (-40°C to +100°C)			
Electrical connection:	Through leads			
Construction:				
Housing:	Chrome plated brass			

All values typical unless otherwise stated



### www.dialight.com | MDEL676CR\_B



#### **Panel Mount Indicator Dimensions**

## Figure 1





Figure 2



#### Dimensions are in mm

Part Number	Color	Voltage (VDC)	Current (mA)	Typical Intensity (mcd)	LED Position	Figure
676-1111-110F	Red	2	20	7720	Protruding	1
676-1211-110F	Green	3.3	20	10100	Protruding	1
676-1311-110F	Orange	2	20	7810	Protruding	1
676-1411-110F	Blue	3.3	20	2980	Protruding	1
676-1511-110F	White	3.3	20	6150	Protruding	1
676-2111-110F	Red	2	20	5650	Recessed	2
676-2211-110F	Green	3.3	20	11520	Recessed	2
676-2311-110F	Orange	2	20	7810	Recessed	2
676-2411-110F	Blue	3.3	20	3810	Recessed	2
676-2511-110F	White	3.3	20	6220	Recessed	2

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at www.dialight.com/Assets/Brochures\_And\_Catalogs/Illumination/MDEL676CR.pdf

Warranty Statement: EXCEPT FOR THE WARRANTY EXPRESSLY PROVIDED FOR [HEREIN/ABOVE/BELOW], DIALIGHT DISCLAIMS ANY AND ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, TITLE, AND NONINFRINGEMENT.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

<u>676-2111-110F</u> <u>676-1111-110F</u> <u>676-1211-110F</u> <u>676-2511-110F</u> <u>676-2411-110F</u> <u>676-2311-110F</u> <u>676-1311-110F</u> 676-1511-110F <u>676-1411-110F</u> <u>676-2211-110F</u>