NOTES:
I. LEAD SPACING MEASURED NEAR EPOXY PACKAGE.

2. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS).
MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY,
HANDLING AND STORAGE IN ACCORDANCE WITH IPC-A-610.

3. SOLDER ADHERANCE: BOTH LEADS PER


MIL. STD. 202E, METHOD 208C, EXCEPT STEAM AGING.
4. LED LEAD FINISH TIN(Sn)/NICKEL(Ni) ON COPPER(Cu).

5. LEDS PACKAGED IN BULK

6. PACKAGE TO HAVE LABEL SHOWING DIALIGHT PART NUMBER, QTY PER BAG, DATE CODE, COUNTRY OF ORIGIN, AND INTENSITY BIN, COLOR BIN AND LOT NUMBER. IF APPLICABLE

7. PART NUMBER WITH "F" SUFFIX ENDING IS ROHS COMPLIANT.
THE BAG PACKAGING IS MARKED WITH "ROHS COMPLIANT" LABEL OR EQUIVALENT MARKINGS. PART CAN BE WAVE SOLDERED, DIP SOLDERED OR HAND SOLDERED USING TYPICAL LEAD-FREE SOLDERING PROCESS WITH MAX. 260°C TEMPERATURE

DIALIGHT P/N	DIFFUSED LENS COLOR	PEAK EMISSION WAVELENGTH (nm)	DOMINANT WAVELENGTH (nm) TYP.	ENGTH ANGLE (°)		(mcd)@I <sub>F</sub> = 2 mA; 25°C		VOLTAGE = 2 mA; 25°C	REVERSE CURRENT (μΑ); 25°C		REVISIONS		
		(11117)	(11117)	2 9 1/2	MIN.	TYP.	TYP.	MAX.	MAX.	REV	DRN.	DATE	
521-9324F	RED	635		60	1.0	1.6	1.7	2.2	10 @ V <sub>R</sub> = 5 V	A	00	11-10-06	
521-9326F	GREEN	565		60	1.0	1.6	1.9	2.2	10 @ V <sub>R</sub> = 5 V	Α	00	11-10-06	
521-9325F	YELLOW	591	587	60	2.3	5.0	1.8	2.4	100 @ V <sub>R</sub> = 5 V	A	00	11-10-06	



ABSOLUTE MAXIMUM RATINGS AT 25° C AMBIENT		UNITS		
ADSOLUTE MAXIMUM RATINOS AT 25°C AMBIENT	521-9324F	521-9326F	521-9325F	UNITS
POWER DISSIPATION	20	20	7.5	mW
CONTINUOUS FORWARD CURRENT	7	7	30	mA
PEAK FORWARD CURRENT (I/IO DUTY CYCLE, O.I ms PULSE WIDTH)	500	500	60	mΑ
REVERSE VOLTAGE	5			٧
SOLDERING TEMPERATURE (.063/(1.60) FROM BODY	260°C FOR 5 SEC			°C
OPERATING TEMPERATURE	- 55 T(	001+ C	-40 TO +100	°C
STORAGE TEMPERATURE	-55 TO +100			°C



REV ECN NO

REVISIONS

NEW RELEASE

DRN CKD APP QA CM

10 0

DATE

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.

FORBIDDEN WITH	OUT THE WRITTEN CONSENT OF DIALIGHT						
SCALE: DRAWING SCALE	DRAWING NUMBER	REV					
ALL DIM'S IN: INCHES (MM)	$\sim$ 17441	۸					
TOLERANCES: UNLESS OTHERWISE SPECIFIED	C - I 7 4 4 I	А					
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005	TITLE 3mm Ø DIFFUSED LED low current ROHS COMPLIANT						
DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL						
FINISH:	Dialight 1501 ROUTE FARMINGDALE,						

SHEET I OF I FAMILY TABLE:

83330

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

521-9324F 521-9325F