



Part Number: MM35 0R560-DIN



Electrical Specifications:

| | |
|--|---------------|
| Resistance @ 25°C | 0.5 Ω ± 25 % |
| Max Steady State Current Up to 65°C | 60.0 A |
| Max recommended energy rating (Joules) | 1200.0 Joules |
| Rhot @100% Steady State Current | 0.008Ω |
| Rhot @75% Steady State Current | 0.011Ω |
| Rhot @50% Steady State Current | 0.020Ω |
| Rhot @25% Steady State Current | 0.052Ω |
| Body Temperature @ 100% Current rating | 217°C |
| Max Recommended Voltage | 680V |
| Material Type | B |
| Max Power | 38.4W |



Mechanical Specifications:

| | |
|--------------------|------------|
| D | 68.0mm Max |
| T | 9.5mm Max |
| S | 34.0mm Nom |
| L | 40.0mm Nom |
| A (Lead Width) | 9.6mm Nom |
| B | 6.0mm Nom |
| C (Lead Thickness) | 0.8mm Nom |
| E | 5.7mm Nom |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[MM35 0R560](#) [MM35 0R560-DIN](#)