

SOLID PC 2828 13 G



Sample photo

Order symbol: PC 2828 13 G
Product nbr: 5330362
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005526
El. number:
Finland: 3423713
Italy: 7401040
Sweden: 2539418

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		278	278	130	Ingress Protection (EN 60529): IP 66/67
inch:		10.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
Material:		Polycarbonate			Electrical insulation: Totally insulated
Base colour:		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
Cover colour:		RAL 7035			UV resistance: UL 508
Cover screws material:		Polyamide			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws colour:		Grey			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		Polyurethane			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
Temperatures:					
Short term:		-40 ... 120 °C			Certificates: Underwriters Laboratories Fimko Europe EN 62208: 2003
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKOVT		Mounting plate			
EKV 22		DIN-35 Mounting rail			
EKOZR		Extension frame			

