



FEATURES:

- This cable assembly is similar to our model 2249-C except with right angle connectors.
- It is designed to access those BNC connectors in tight locations such as found in the back of rack mounted equipment.
- The right angle connectors are impedance matched to provide the best signal quality.
- These cables are made of the highest quality materials and assembly procedures.

MATERIALS:

BNC: Body: Brass, tarnish resistant plating
 Center Contacts: Brass, gold plating
 Strain Relief: PVC, molded onto cable and connector
 Cable: RG58C/U, 50 Ohm, .195 OD

RATINGS:

Voltage:Shield/Earth: 30VAC/60VDC Max.
 Inner Conductor/Shield: 500VRMSMax.
 Operating Temperature: +50° C (+122° F)
 Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4276-C-XX

XX = Cable length in inches
 Std. Lengths: 12" (30,5 cm), 24" (61 cm), 36" (91.44 cm)
 Additional lengths can be quoted upon request.
 Ordering Example: 4276-C-36 is a cable with a length of 36"

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4276-C-36](#) [4276-C-12](#) [4276-C-24](#)