

2014220

LAZER CT™ Reciprocating Saw Blade 152 x 25 x 1.3mm 8 TPI

Carbide tipped metal cutting reciprocating saw blades for the highest performance in cast iron and stainless steel. High performance carbide provides up to 10X life vs. standard Lenox bi-metal reciprocating saw blades. Engineered to deliver fast and straight straight cuts in demanding materials.

Selling Propositions

- UP TO 10X LONGER LIFE THAN BI-METAL RECIPROCATING BLADES* - High performance carbides are welded to increase durability and prevent tooth loss
- STRAIGHT CUTS IN LARGE DIAMETER MATERIALS - Tall blade profile delivers straight cuts and long life in demanding metal cutting applications
- ENGINEERED FOR FAST PERFORMANCE - Each tooth is precision ground to quickly cut through difficult metals

Standard Equipment

Warranty specifications

- Not Applicable (Statutory Rights Not Affected)

Specifications	
TPI	8
Length	152.0 mm
Width	25.0 mm
Thickness	1.3 mm
Master Pack	150.0
Min. Order Qty Blades/Pack	1.0
Applications	All metals
Order unit = pack	1.0
Cutting Range	>2 mm
Type	6108RCT