



used for:



MATERIAL:

INSULATOR : PBT +30% GLASS FIBER (UL 94V-0)
 CONTACT : PHOSPHOR BRONZE
 CONTACT FINISH : GOLD ON MATING END, TIN ON TERMINATION END,
 WITH ENTIRE CONTACT NICKEL UNDERPLATED
 SHELL : BRASS, NICKEL PLATED
 @BACK SHELL : STEEL, NICKEL PLATED
 BOTTOM COVER : NYLON, BLACK


SPECIFICATION:

CURRENT RATING : 1.5AMP
 DIELECTRIC WITHSTANDING VOLTAGE : 500V AC
 INSULATION RESISTANCE : 1000MΩ MIN.
 CONTACT RESISTANCE BEFORE : 30mΩ MAX
 CONTACT RESISTANCE AFTER : 50mΩ MAX
 OPERATING TEMPERATURE : -20°C ~ +85°C



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.

DO NOT ALTER CAD DRAWING BY HAND		tolerance	finish	scale:
Denote: .xxx	unless otherwise specified tolerance shall be as follow	Angles:	Dim. in mm	material: SEE MATERIAL
rev./description	a	1	date	title:
origin	1	Oct/25/06	drawn	USB Connector A female type
date	K.Santangelo	May 09	appd.	PCB R/A (Triple)
name	R. Santangelo	norm	q-ctrl	RoHS compliant
drawing no.:		AutocAD 2005		DIN A3
part no.:		39K1A243		sheet 1/1
33UBAR-TSNIR				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[33UBAR-TSN1R](#)