

Product data sheet

Specifications



Mureva BOX - junction box - without - 80x80x45 mm

ENN05044

Main

Product range	Mureva BOX
Product type	Junction box
Colour	Grey (RAL 7035)
Quantity per package	5 pieces

Complementary

Mounting	Surface
Cable entry	Without
Fixing mode	Clip-on: cover
Inner dimensions	80 x 80 x 45 mm
Material	ABS (acrylonitrile butadiene-styrene): body PP (polypropylene): cover
Electrical insulation class	Class II conforming to IEC 536
Height	51 mm
Width	89 mm
Depth	89 mm
Net weight	0.064 kg

Environment

Operating temperature	-25...40 °C
IP-Class	IP55 conforming to IEC 60529
IK-Class	IK07 conforming to EN 50102
Glow wire temperature	650 °C
Standards	EN 60670 CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	8.9 cm

Package 1 Length	8.9 cm
Package 1 Weight	68.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Height	32.0 cm
Package 2 Width	36.5 cm
Package 2 Length	498.0 cm
Package 2 Weight	6.8 kg
Unit Type of Package 3	P12
Number of Units in Package 3	3000
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	216.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)