

Ferrite Shallow Pot Magnets



These pot magnets are known as female threaded stud pot magnets because the internal threaded hole could take pot magnets with threaded bar at the back (external threaded stud pot magnets / male threaded stud pot magnets) as well as bolts. They consist of a ferromagnetic mild steel cup containing a magnet (usually a disc magnet) with a ferromagnetic mild steel stud / boss / bush mounting at the back of the pot magnet into which a threaded hole has been made.



- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with zinc plated body
- Female thread

RS PART NO	ECLIPSE PART NO	PULL FORCE (KG)	DESCRIPTION
9093616	E861RS	1.0	13mm dia (pr)
9093610	E866RS	10.0	36mm dia (pr)
9093629	E868RS	18.0	47mm dia (pk 1)
9093622	E870RS	28.0	57mm dia (pk 1)
	E873RS	70.0	90mm dia (pk 1)
	E874RS	90.0	100mm dia (pk 1)
	E875RS	130.0	125mm dia (pk 1)

All sizes and colours available from stock. Please get in touch for further information.

Eclipse Magnetics, Atlas Way, Sheffield, S4 7QQ, England
T +44(0)114 225 0613 info@eclipsemagnetics.com
F +44(0)114 225 0610 www.eclipsemagnetics.com



A world leader in magnetic technology

