


Mod. 7745.B

COPOLYMER POLYPROPYLENE WATERPROOF CASE

Light, water and dust tight cases. Floating and submersible until one meter (certified IP 67). Shipping label holder, two man lift side handles and retractable handle. Self-oiling free running wheels.



METRIC MM-KG-C°



INTERNAL DIMENSIONS

L LENGTH	770 mm
W WIDTH	580 mm
D DEPTH	450 mm
LID	90 mm
BASE	360 mm


EXTERNAL DIMENSIONS

L LENGTH	836 mm
W WIDTH	641 mm
D DEPTH	489 mm

OTHER DATA

WEIGHT EMPTY	15.50 Kg
WEIGHT WITH FOAM	19.80 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	200 lt
BUOYANCY	144 Kg/max
OPERATING TEMPERATURE	°C min -33 / max +90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS

L LENGTH	30 5/16 in
W WIDTH	22 13/16 in
D DEPTH	17 11/16 in
LID	3 9/16 in
BASE	14 3/16 in

EXTERNAL DIMENSIONS

L LENGTH	32 15/16 in
W WIDTH	25 1/4 in
D DEPTH	19 1/4 in

OTHER DATA

WEIGHT EMPTY	34.17 lbs
WEIGHT WITH FOAM	43.65 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	52.83 gal
BUOYANCY	317.47 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max +194