


AVERY DENNISON MARKETING SPECIFICATION

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS UNLAWFULLY DISCLOSED TO OTHERS. ANY REPRODUCTION OR USE OF THIS PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY, IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

REV.	DATE	DESCRIPTION
B	12.16.14	UPDATE FORMAT, CHG DIM 5 AND ADDED NOTE TO DIM 5; ADDED UL LOGO AND FLAME RATING NOTE



UL us

LISTED
POSITIONING DEVICE
E57800
TYPE 21

NOTE: THESE CABLE TIES ARE UV RESISTANT AND HAVE A FLAMMABILITY RATING OF V-2

MILITARY STANDARD:	MS-3367-3-0
LOOP TENSILE STRENGTH:	120 LBF /534N MIN. PER AS-23190
OPERATING TEMP:	-40°F(-40°C) TO 176°F (80°C)
MIN. INSTALLATION TEMP:	32 °F(0 °C)
WEIGHT:	.155 OZ./4.58g
BUNDLE DIAMETER:	ø4.7mm(.19in) TO ø101.6mm(4.00in)
TOOL:	12001 - HAND INSTALLATION TOOL 12500 - PNEUM. INSTALLATION TOOL
TOOL TENSION SETTING:	6 - 8 ON HEAVY DUTY TOOL
PACKAGING:	50/BAG, 1000/CASE

APPROVALS:	ENG. APPR. <i>[Signature]</i> 12/16/14
SPECIFIED TOLERANCES ARE:	G.A. APPR. <i>[Signature]</i> 12-16-14
	MATERIAL
.XX ± .03 IN.	NYLON 6/6, WEATHER RESISTANT
.XXX ± .010 IN.	COLOR
ANGULAR: ± 2°	BLACK

AVERY DENNISON	DESCRIPTION
FASTENER DIVISION FRITCHBURG, MA 01540 U.S.A. TEL: 1-800-225-9713 FAX: 978-353-6157	14.5" CABLE TIE, HEAVY DUTY
STOCK NO.	REV.
08382-0	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[08382-0](#)