



Pos.	A	B	C	COLOR	PART NO.
3	8.5	2	5.0	BLUE 青	4- -3
7	18.5	6	15.0		2- -7
5	13.5	4	10.0		2- -5
3	8.5	2	5.0		2- -3
2	6.0	1	2.5	BLACK 黒	2- -2
20	51.0	19	47.5		2- -0
18	46.0	17	42.5		1- -8
17	43.5	16	40.0		1- -7
16	41.0	15	37.5		1- -6
15	38.5	14	35.0		1- -5
14	36.0	13	32.5		1- -4
13	33.5	12	30.0		1- -3
12	31.0	11	27.5		1- -2
11	28.5	10	25.0		1- -1
10	26.0	9	22.5		1- -0
9	23.5	8	20		-9
8	21.0	7	17.5		-8
7	18.5	6	15		-7
6	16.0	5	12.5		-6
5	13.5	4	10		-5
4	11.0	3	7.5		-4
3	8.5	2	5		-3
2	6.0	1	2.5	NATURAL 自然色	172520 -2

- 注:
- 使用端子は型番 172781
172782
 - 通用製品規格: 108-5163
 - 取扱説明書: IS-207J
-208J
- △ カット端: 0.4 最大
 △ 成形上必要は溝 (オプション)
 △ AMP-台湾のみの製造品

- NOTES:
- APPLICABLE CONTACT: 172781
172782
 - PRODUCT SPEC: 108-5163
 - INSTRUCTION SHEET: IS-207J
-208J
- △ CUTTING END: 0.4 MAX.
 △ THIS GROOVE IS OPTIONAL.
 △ PRODUCTION ITEMS OF AMP TAIWAN ONLY.



適合電線範囲 (WIRE RANGE)	絶縁外径 (INSULATION DIA.)	品名 (NAME)
mm (AWG)	mm	ロープロファイルミニコネクタ (25ピッチ) (HEADER HOUSING, LOW PROFILE MINI AMP-IN 25 PITCH)
材料 (MATERIAL)	仕上 (FINISH)	規格 (SPEC.)
NYLON (UL94-0)		SIZE LOC 番号 (NO.) A3 J C-172520
DR. S. Kato 8/23/85	DE	REV. G2 SHEET
CHK. M. Aoki 8/23/85	APP. N. Oishi 9/8/85	尺 (SCALE) 10-1

G2	REVISED PER ECO-11-005030	RK	HMR	25MAR 11
LTR	変更 (REVISION RECORD)	DR	CHK (DATE)	

寸法: TL DIMENSIONS IN MM. DO NOT SCALE PRINT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172520-3](#)