

# M18 FHZ-0X

## M18 FUEL™ HACKZALL™

- POWERSTATE™ brushless motor provides increased efficiency, lasts longer and delivers maximum power
- REDLINK PLUS™ intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life
- 22 mm stroke length for controlled cutting with a no load stroke rate of 3000 spm
- Pivoting shoe allows the user to optimise his cutting position
- Built in LED light improves visibility in low light cutting applications
- Patented FIXTEC™ clamp for quick and efficient blade change
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



### REDLITHIUM™

|                           |                                                    |
|---------------------------|----------------------------------------------------|
| No load stroke rate (spm) | 0 - 3000                                           |
| Stroke length (mm)        | 22                                                 |
| Kit included              | No batteries supplied, No charger supplied, HD Box |
| Article Number            | 4933459887                                         |