

SRT3000RMXLA

APC Smart-UPS On-Line, 3kVA, Rackmount
2U, 120V, 8x 5-20R+1x L5-30R NEMA outlets,
SmartSlot, Extended runtime, W/ rail kit



Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	2700 W
Rated power in VA	3000 VA
Input Connection Type	NEMA L5-30P
Nb of power socket outlets	8 NEMA 5-20R 1 NEMA L5-30R
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack Mounting brackets Rack Mounting support rails USB cable Warranty card

General

Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	25.00 in (63.5 cm)
Net Weight	69.00 lb(US) (31.3 kg)
Mounting Location	Front
Mounting preference	Lower

Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

Input

Input Frequency	40 - 70 Hz auto-sensing
-----------------	-------------------------

Output

Max Configurable Power (Watts)	2700 W
Harmonic distortion	Less than 2%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave
Bypass type	Internal Bypass (Automatic and Manual)
Maximum configurable power in VA	3000 VA

Conformance

Product Certifications	ENERGY STAR V2.0 (USA)
Standards	CSA C22.2 No.107.3-05 FCC Part 15 class A OSHDP UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	55 dBA
Heat dissipation	805 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Included Battery Modules	1
Typical recharge time	3 h
RBC Quantity	1
Battery Voltage	96V
Battery Charge Power (Watts)	151 W rated
Battery power in VAh	454 VAh runtime
Battery Life	3...5 year(s)
Battery option	SRT96RMBP 1 1362 VAh SRT96RMBP 2 2270 VAh SRT96RMBP 3 3178 VAh SRT96RMBP 4 4086 VAh SRT96RMBP 5 4994 VAh SRT96RMBP 6 5902 VAh SRT96RMBP 8 7718 VAh SRT96RMBP 10 9534 VAh
Extendable Run Time	1

Communications & Management

Free slots	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	340 J
---------------------	-------

Ordering and shipping details

GTIN	731304323068
Package weight(Lbs)	88.01 lb(US) (39.92 kg)

Packing Units

Package 1 Height	9.69 in (24.6 cm)
Package 1 width	23.58 in (59.9 cm)
Package 1 Length	34.29 in (87.1 cm)
Number of Units in Package 3	6

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT3000RMXLA](#)