





BOSCH

INNOVATIVE BLADES FOR EVERY CUT

Jigsaw blades by Bosch.

www.bosch-professional.com

The best your tool can get. Bosch Professional Accessories.



70 YEARS OF EXPERIENCE – MADE IN SWITZERLAND



Bosch developed the first jigsaw – and then reinvented it again and again. Whether you need a tool for precise sawing with accurate angles or for robust use: At Bosch, craftsmen will find the right jigsaw for every application.

Bosch has been selling saw blades from our own development and production since 1947. Leading technology and extensive experience in the production of jigsaw and sabre saw blades have always been the foundation. Unrivalled quality and innovation make your saw blade even more versatile and durable. Be part of our success story and discover our unique saw blades.

- ▶ Quality from Switzerland
- ▶ Modern production and testing technology
- ▶ Innovative technologies for significantly longer performance lifetime than with other saw blades



BOSCH CARBIDE TECHNOLOGY

Professional solutions
for the toughest requirements.

CARBIDE TECHNOLOGY

Up to 20 times longer performance lifetime in the hardest materials!
The new jigsaw blades from Bosch with unique carbide technology guarantee maximum durability – cut by cut.

Bimetal saw blades

20×



VS

1×

Saw blade with Bosch
carbide technology



These professional jigsaw blades cut through solid and toughest materials
whereas conventional bimetal saw blades fail quickly.





WOOD

WOOD AND METAL

METAL



PLASTICS



SPECIAL APPLICATIONS

SETS

SYSTEM ACCESSORIES

JIGSAW BLADES FOR WOOD



Single lug shank


EXTRA-CLEAN FOR WOOD

For double-sided sawing without tearing

T 308 B



- ▶ HCS, total length 117 mm, extra-clean sawing
- ▶ for softwood and non-abrasive wood materials (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 663 750	3 165 140 470 278
5 pieces	2 608 663 751	3 165 140 470 285

Pack quantity	Order no.	EAN
25 pieces	2 608 663 752	3 165 140 470 292
100 pieces	2 608 663 753	3 165 140 470 308

T 308 BO



- ▶ HCS, total length 117 mm, extra-clean curved cuts
- ▶ for softwood and non-abrasive wood materials (5–50 mm)



Pack quantity	Order no.	EAN
3 pieces	2 608 663 867	3 165 140 535 779
5 pieces	2 608 663 868	3 165 140 535 786

Pack quantity	Order no.	EAN
25 pieces	2 608 663 869	3 165 140 535 793


CLEAN FOR WOOD

Clean cuts

T 101 AO



- ▶ HCS, total length 83 mm, extra-clean curved cuts
- ▶ for softwood and non-abrasive wood materials (1.5–15 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 630 559	3 165 140 006 972
5 pieces	2 608 630 031	3 165 140 006 798

T 101 B



- ▶ HCS, total length 100 mm, no tears on the underside of the material
- ▶ for softwood and non-abrasive wood materials (3–30 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 630 557	3 165 140 006 958
5 pieces	2 608 630 030	3 165 140 006 781

Pack quantity	Order no.	EAN
25 pieces	2 608 633 622	3 165 140 127 660
100 pieces	2 608 637 876	3 165 140 067 430

T 101 BR



- ▶ HCS, total length 100 mm, no tears on the upper side of the material
- ▶ for softwood and non-abrasive wood materials (3–30 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 633 779	3 165 140 091 374
5 pieces	2 608 630 014	3 165 140 012 454

Pack quantity	Order no.	EAN
25 pieces	2 608 633 623	3 165 140 127 677

T101 D



- ▶ HCS, total length 100 mm, no tears on the underside of the material
- ▶ for softwood and non-abrasive wood materials (10–45 mm)




Pack quantity	Order no.	EAN
3 pieces	2608630558	3165140006965
5 pieces	2608630032	3165140006804

Pack quantity	Order no.	EAN
25 pieces	2608633577	3165140148726
100 pieces	2608637877	3165140067447

T301 CD



- ▶ HCS, total length 117 mm, no tears on the underside of the material
- ▶ for softwood and non-abrasive wood materials (10–65 mm)



Pack quantity	Order no.	EAN
3 pieces	2608637591	3165140016315
5 pieces	2608637590	3165140016308


PROGRESSOR FOR WOOD

Universal. Clean cuts in thin and thick materials

T234X



- ▶ HCS, total length 117 mm, clean cuts through thin and thick materials
- ▶ for softwood and non-abrasive wood materials (3–65 mm)



Pack quantity	Order no.	EAN
3 pieces	2608633523	3 165 140 169 493
5 pieces	2608633528	3 165 140 169 509

Pack quantity	Order no.	EAN
25 pieces	2608633524	3 165 140 169 516
100 pieces	2608633A41	3 165 140 264 242


ENDURANCE FOR WOOD

Outstanding performance lifetime and fast cuts

T144DHM



- ▶ HM, total length 100 mm, fast straight cuts
- ▶ for softwood, hardwood, WPC, MDF/HDF, chipboards, cement fibre boards (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2608665071	3 165 140 997 713


PRECISION FOR WOOD

Accurate angular cuts

T 308 BP



- ▶ HCS, total length 117 mm, extra-clean and accurate angular cuts
- ▶ for softwood and non-abrasive wood materials (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 667 399	3 165 140 623 650
5 pieces	2 608 667 400	3 165 140 623 667

T 301 BCP



- ▶ HCS, total length 117 mm, clean and accurate angular cuts
- ▶ for softwood and non-abrasive wood materials (3–65 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 633 A33	3 165 140 264 167
5 pieces	2 608 633 A37	3 165 140 264 204

Pack quantity	Order no.	EAN
25 pieces	2 608 633 A40	3 165 140 264 235

T 144 DP



- ▶ HCS, total length 100 mm, fast straight and accurate angular cuts
- ▶ for softwood and non-abrasive wood materials (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2 608 633 A31	3 165 140 264 143
5 pieces	2 608 633 A35	3 165 140 264 181

Pack quantity	Order no.	EAN
25 pieces	2 608 633 A39	3 165 140 264 228
100 pieces	2 608 633 A42	3 165 140 264 259

T 344 DP



- ▶ HCS, total length 152 mm, fast straight and accurate angular cuts
- ▶ for thick construction timber, softwood and non-abrasive wood materials (5–100 mm)




Pack quantity	Order no.	EAN
3 pieces	2608633A32	3 165 140 264 150
5 pieces	2608633A36	3 165 140 264 198

T 1044 DP



- ▶ HCS, total length 250 mm, fast straight and accurate angular cuts
- ▶ for thick construction timber, softwood and non-abrasive wood materials (5–150 mm)



Pack quantity	Order no.	EAN
3 pieces	2608667394	3 165 140 623 605


SPEED FOR WOOD

Fast cutting

T 144 D



- ▶ HCS, total length 100 mm, fast straight cuts
- ▶ for softwood and non-abrasive wood materials (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2608630560	3 165 140 006 989
5 pieces	2608630040	3 165 140 006 842

Pack quantity	Order no.	EAN
25 pieces	2608633625	3 165 140 127 691
100 pieces	2608637880	3 165 140 067 478

T244D

- ▶ HCS, total length 100 mm, rough, fast curved cuts
- ▶ for softwood and non-abrasive wood materials (5–50 mm)

Pack quantity	Order no.	EAN
3 pieces	2608630879	3165140007221
5 pieces	2608630058	3165140006859




Pack quantity	Order no.	EAN
25 pieces	2608633626	3165140127707
100 pieces	2608637881	3165140067485

T344D


- ▶ HCS, total length 152 mm, fast straight cuts
- ▶ for thick construction timber, softwood and non-abrasive wood materials (5–100 mm)

Pack quantity	Order no.	EAN
3 pieces	2608637944	3165140070942
5 pieces	2608633A34	3165140264174

**T744D**

- ▶ HCS, total length 180 mm, fast straight cuts
- ▶ for thick construction timber, softwood and non-abrasive wood materials (5–135 mm)

Pack quantity	Order no.	EAN
3 pieces	2608663314	3165140348591



JIGSAW BLADES FOR HARDWOOD



Single lug shank


EXTRA-CLEAN FOR HARDWOOD

For double-sided sawing without tearing

T 308 BF



- ▶ BIM, total length 117 mm, extra-clean sawing
- ▶ for hardwood, abrasive wood materials and kitchen counters (5–50 mm)



Pack quantity	Order no.	EAN
3 pieces	2608636568	3165140470315
5 pieces	2608636569	3165140470322

Pack quantity	Order no.	EAN
25 pieces	2608636570	3165140470339
100 pieces	2608636571	3165140470346


PRECISION FOR HARDWOOD

Accurate angular cuts

T 308 BFP



- ▶ BIM, total length 117 mm, extra-clean and accurate angular cuts
- ▶ for hardwood, abrasive wood materials and kitchen counters (5–50 mm)



Pack quantity	Order no.	EAN
3 pieces	2608636736	3165140623674
5 pieces	2608636737	3165140623681

CLEAN FOR HARDWOOD


Clean cuts

T 101 AOF



- ▶ BIM, total length 83 mm, extra-clean curved cuts
- ▶ for hardwood and abrasive wood materials (1.5–15 mm)

Pack quantity	Order no.	EAN
3 pieces	2 608 636 225	3 165 140 264 341
5 pieces	2 608 634 233	3 165 140 091 848




T 101 AIF



- ▶ BIM, total length 100 mm, clean sawing
- ▶ for hardwood and abrasive wood materials (2–30 mm)

Pack quantity	Order no.	EAN
3 pieces	2 608 636 224	3 165 140 264 334
5 pieces	2 608 634 897	3 165 140 096 355




T 101 BF



- ▶ BIM, total length 100 mm, no tears on the underside of the material
- ▶ for hardwood and abrasive wood materials (3–30 mm)

Pack quantity	Order no.	EAN
3 pieces	2 608 636 226	3 165 140 264 358
5 pieces	2 608 634 234	3 165 140 091 855




Pack quantity	Order no.	EAN
25 pieces	2 608 634 988	3 165 140 127 714

T 101 BRF



- ▶ BIM, total length 100 mm, no tears on the upper side of the material
- ▶ for hardwood and abrasive wood materials (3–30 mm)




Pack quantity	Order no.	EAN
3 pieces	2608636227	3 165 140 264 365
5 pieces	2608634235	3 165 140 091 862

Pack quantity	Order no.	EAN
25 pieces	2608634989	3 165 140 127 721

T 301 CDF



- ▶ BIM, total length 117 mm, no tears on the underside of the material
- ▶ for hardwood and abrasive wood materials (4–65 mm)



Pack quantity	Order no.	EAN
3 pieces	2608636228	3 165 140 264 372
5 pieces	2608636229	3 165 140 264 389


SPEED FOR HARDWOOD

Fast cutting

T144DF



- ▶ BIM, total length 100 mm, fast straight cuts
- ▶ for hardwood and abrasive wood materials (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2608636222	3165140264310
5 pieces	2608634567	3165140009430

Pack quantity	Order no.	EAN
25 pieces	2608634990	3165140127738

T344DF



- ▶ BIM, total length 152 mm, fast straight cuts
- ▶ for thick construction timber, hardwood and abrasive wood materials (5–100 mm)



Pack quantity	Order no.	EAN
3 pieces	2608636223	3165140264327
5 pieces	2608634243	3165140091947


ENDURANCE FOR LAMINATE

Outstanding performance lifetime and clean cuts

T 128 BHM



- ▶ HM, total length 92 mm, outstanding performance lifetime
- ▶ for very hard laminates, glass fibre-reinforced vinyl and HPL, e.g. Trespa® (2–15 mm)



Pack quantity	Order no.	EAN
3 pieces	2608665073	3165140997720


SPECIAL FOR LAMINATE

Clean cuts

T 101 AOF



- ▶ BIM, total length 83 mm, extra-clean curved cuts
- ▶ for laminates, multiplex panels (1.5–15 mm)




Pack quantity	Order no.	EAN
3 pieces	2608636432	3165140393423

T 101 BIF



- ▶ BIM, total length 83 mm, clean sawing
- ▶ for laminates, multiplex panels (1.5–15 mm)



Pack quantity	Order no.	EAN
5 pieces	2608636431	3165140393416

JIGSAW BLADES FOR WOOD AND METAL



Single lug shank






PROGRESSOR FOR WOOD AND METAL

Universal. Fast cuts in thin and thick materials

T 367 XHM



- ▶ HM, total length 132 mm, cuts through thin and thick materials
- ▶ for example, for hardened steel screws and nails in construction timber (<65 mm) and sheet metals (4–10 mm)




Pack quantity	Order no.	EAN
3 pieces	2608667562	3165140846622

T 345 XF



- ▶ BIM, total length 132 mm, fast cuts through thin and thick materials
- ▶ for example, for nails in construction timber (<65 mm) and sheet metals (3–10 mm)



Pack quantity	Order no.	EAN
3 pieces	2608634993	3165140128018
5 pieces	2608634994	3165140128025

Pack quantity	Order no.	EAN
25 pieces	2608634995	3165140128032
100 pieces	2608634486	3165140266208

WOOD AND METAL



JIGSAW BLADES FOR METAL



Single lug shank

SPEED FOR METAL


Durable and fast

T 121 GF



- ▶ BIM, total length 92 mm, extra-fast cuts
- ▶ for very thin sheet metals (0.5–1.5mm)

Pack quantity	Order no.	EAN
3 pieces	2 608 636 695	3 165 140 596 824
5 pieces	2 608 636 696	3 165 140 596 831




Pack quantity	Order no.	EAN
25 pieces	2 608 636 697	3 165 140 596 848

T 121 AF



- ▶ BIM, total length 92 mm, extra-fast cuts
- ▶ for thin sheet metals (1–3 mm)

Pack quantity	Order no.	EAN
3 pieces	2 608 636 698	3 165 140 596 855
5 pieces	2 608 636 699	3 165 140 596 862




Pack quantity	Order no.	EAN
25 pieces	2 608 636 700	3 165 140 596 947

T 121 BF



- ▶ BIM, total length 92 mm, extra-fast cuts
- ▶ for medium-thick sheet metals (2.5–6 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636701	3165140596954
5 pieces	2608636702	3165140596961




Pack quantity	Order no.	EAN
25 pieces	2608636703	3165140596978

T 321 AF



- ▶ BIM, total length 132 mm, extra-fast cuts
- ▶ for thin sheet metals (1–3 mm) and thin-walled pipes and profiles (<math>< \varnothing 65 \text{ mm}</math>)

Pack quantity	Order no.	EAN
3 pieces	2608636704	3165140596985
5 pieces	2608636705	3165140596992




T 321 BF



- ▶ BIM, total length 132 mm, extra-fast cuts
- ▶ for medium-thick sheet metals (2.5–6 mm) and thick-walled pipes and profiles (<math>< \varnothing 65 \text{ mm}</math>)

Pack quantity	Order no.	EAN
3 pieces	2608636706	3165140597005
5 pieces	2608636707	3165140597012



PROGRESSOR FOR METAL


Universal. Fast cuts in thin and thick materials

T 123 XF



- ▶ BIM, total length 100 mm, fast cuts through thin and thick materials
- ▶ for thin to thick sheet metals (1.5–10 mm), pipes and profiles (<math>< \varnothing 30 \text{ mm}</math>)

Pack quantity	Order no.	EAN
3 pieces	2608638472	3165140128049
5 pieces	2608638473	3165140128056



Pack quantity	Order no.	EAN
25 pieces	2608638474	3165140128063
100 pieces	2608638700	3165140264488

FLEXIBLE FOR METAL


For curved cuts in metal

T 118 EOF



- ▶ BIM, total length 83 mm, specifically for curved cuts
- ▶ for thin sheet metals (1,5–4 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636231	3165140264402
5 pieces	2608634237	3165140091893



ENDURANCE FOR STAINLESS STEEL


Long performance lifetime in stainless steel

T 118AHM




- ▶ HM, total length 83 mm, outstanding performance lifetime
- ▶ for thin sheets made of Inox stainless steel / (1.5–3 mm)

Pack quantity	Order no.	EAN
3 pieces	2608630663	3165140017749




T 118EHM



- ▶ HM, total length 83 mm, outstanding performance lifetime
- ▶ for medium-thick sheets made of Inox stainless steel / (2–5 mm)

Pack quantity	Order no.	EAN
3 pieces	2608630665	3165140017756



BASIC FOR INOX


For stainless steel

T 118 GFS



- ▶ BIM, total length 83 mm
- ▶ for thin sheets made of Inox stainless steel / (0.5–1,5 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636498	3 165 140 451 864
5 pieces	2608636496	3 165 140 451 840




T 118 EFS



- ▶ BIM, total length 83 mm
- ▶ for medium-thick sheets made of Inox stainless steel / (1,5–4 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636499	3 165 140 451 871
5 pieces	2608636497	3 165 140 451 857



SPECIAL FOR ALUMINIUM


For Aluminium and Non-Ferrous Metals

T 227 D



- ▶ HSS, total length 100 mm, curved cuts in aluminium
- ▶ for thin to thick sheet metals made of aluminium (3–15 mm), aluminium pipes and profiles (<math>< \varnothing 30 \text{ mm}</math>)

Pack quantity	Order no.	EAN
3 pieces	2608631671	3165140007535
5 pieces	2608631030	3165140007320




Pack quantity	Order no.	EAN
100 pieces	2608638382	3165140279475

T 127 D



- ▶ HSS, total length 100 mm, big tooth pitch specifically for aluminium
- ▶ for thin to thick sheet metals made of aluminium (3–15 mm), aluminium pipes and profiles (<math>< \varnothing 30 \text{ mm}</math>)

Pack quantity	Order no.	EAN
3 pieces	2608631508	3165140007405
5 pieces	2608631017	3165140007313



Pack quantity	Order no.	EAN
100 pieces	2608631966	3165140067515

FLEXIBLE FOR METAL-SANDWICH


Break-proof and durable

T 718 BF



- ▶ BIM, total length 180 mm, break-proof and durable
- ▶ for metal-sandwich panels (< 120 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636335	3165140309042



PRECISION FOR METAL-SANDWICH


Break-proof and durable, accurate angle cutting

T 1018 AFP



- ▶ BIM, total length 250 mm, accurate angular cuts
- ▶ for metal-sandwich panels (< 150 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636793	3165140704892



JIGSAW BLADES FOR PLASTICS



Single lug shank


CLEAN FOR PP

Clean cuts

T 102 D



- ▶ HCS, total length 100 mm, no melting and rewelding
- ▶ for PP and PE sheets (5–30 mm), profiles and bars (<math>< \varnothing 30 \text{ mm}</math>)



Pack quantity	Order no.	EAN
3 pieces	2608667443	3165140691475
5 pieces	2608667444	3165140691482


CLEAN FOR PVC

Clean cuts without continuous chip formation

T 102 H



- ▶ HCS, total length 100 mm, no continuous chip formation
- ▶ for PVC, PA and PS sheets (3–30 mm), profiles and bars (<math>< \varnothing 30 \text{ mm}</math>)




Pack quantity	Order no.	EAN
3 pieces	2608667445	3165140691499
5 pieces	2608667446	3165140691505

T 302 H



- ▶ HCS, total length 132 mm, no continuous chip formation
- ▶ for PVC, PA and PS sheets (3–65 mm), profiles and bars (<math>< \varnothing 65 \text{ mm}</math>)


Pack quantity	Order no.	EAN
3 pieces	2608667447	3165140691512
5 pieces	2608667448	3165140691529



PRECISION FOR PVC


Accurate angular cuts

T 1044 HP



- ▶ HCS, total length 250 mm, accurate angular cuts
- ▶ for PVC, PA and PS pipes and profiles (<math>< 160 \text{ mm}</math>)

Pack quantity	Order no.	EAN
3 pieces	2608667843	3165140814980



CLEAN FOR PMMA


Clean cuts

T 102 BF



- ▶ BIM, total length 92 mm, no rough kerfs
- ▶ for PMMA acrylic sheets (2–20 mm)

Pack quantity	Order no.	EAN
3 pieces	2608636780	3165140691581
5 pieces	2608636781	3165140691598



CLEAN FOR PC


Clean cuts

T 101 A



- ▶ HSS, total length 100 mm, clean cuts
- ▶ for acrylic glass and polycarbonate sheets (2–20 mm)

Pack quantity	Order no.	EAN
3 pieces	2608631670	3165140007528
5 pieces	2608631010	3165140007276






CLEAN FOR CARBON FIBRE

Long performance lifetime in CFRP and FRP composites

T 108 BHM



- ▶ HM, total length 92 mm, outstanding performance lifetime
- ▶ for carbon fibre (CFRP) and glass fibre (FRP) composite sheets (<20 mm)



Pack quantity	Order no.	EAN
3 pieces	2608667449	3165140691536


CLEAN FOR PLASTIC COMPOSITES

Long performance lifetime in wood fibre composites

T 301 CHM



- ▶ HM, total length 117 mm, outstanding performance lifetime
- ▶ for wood fibre composites (WPC) and glass fibre-reinforced plastic (FRP) (<65 mm)



Pack quantity	Order no.	EAN
3 pieces	2608667450	3165140691543



JIGSAW BLADES FOR SPECIAL APPLICATIONS



Single lug shank


ENDURANCE FOR FIBRE PLASTER

Long performance lifetime in cement fibre boards

T 141 HM



- ▶ HM, total length 100 mm, outstanding performance lifetime
- ▶ for plasterboard, cement fibre board (5–50 mm)




Pack quantity	Order no.	EAN
3 pieces	2608633175	3 165 140 109 758

T 341 HM



- ▶ HM, total length 132 mm, outstanding performance lifetime
- ▶ for plasterboard, cement fibre board (5–80 mm)



Pack quantity	Order no.	EAN
3 pieces	2608633176	3 165 140 109 765

SPECIAL APPLICATIONS



SPECIAL FOR CERAMICS


Soft ceramic materials and soft tiles

T 130 RF




- ▶ HM (30 grit), total length 83 mm, straight cuts
- ▶ for soft ceramic wall tiles (5–15 mm)

Pack quantity	Order no.	EAN
3 pieces	2608633104	3 165 140 035 286




T 150 RF



- ▶ HM (50 grit), total length 83 mm, fine adjustment cuts
- ▶ for soft ceramic wall tiles (5–10 mm)

Pack quantity	Order no.	EAN
3 pieces	2608633105	3 165 140 035 293



SPECIAL APPLICATIONS



SPECIAL FOR SOFT MATERIALS


Soft materials

T113A



- ▶ HCS, total length 100 mm, clean cuts
- ▶ for cardboard, polystyrene, carpet, leather and rubber (< 50 mm)

Pack quantity	Order no.	EAN
3 pieces	2608635177	3165140035323




T313AW



- ▶ HCS, total length 152 mm, clean cuts
- ▶ for cardboard, polystyrene, carpet, leather and rubber (< 100 mm)

Pack quantity	Order no.	EAN
3 pieces	2608635187	3165140045926



SPECIAL
APPLICATIONS




PRECISION FOR SOFT MATERIALS

Accurate angular cuts in fibre insulation materials

T 1013 AWP



- ▶ HCS, total length 250 mm, clean and accurate angular cuts
- ▶ for fibre insulation materials (< 150 mm)



Pack quantity	Order no.	EAN
3 pieces	2 608 667 396	3 165 140 623 629

SPECIAL APPLICATIONS



JIGSAW BLADE SETS



Single lug shank

TOUGH BOX

Stabile storage box

WOOD AND METAL, 40 PIECES

- ▶ 10× T 244 D
- ▶ 10× T 144 D
- ▶ 10× T 101 B
- ▶ 10× T 121 AF



Pack quantity	Order no.	EAN
40 pieces	2607010904	3165140846509

WOOD AND METAL, 30 PIECES

- ▶ 10× T 119 BO
- ▶ 10× T 111 C
- ▶ 10× T 118 A



Pack quantity	Order no.	EAN
30 pieces	2607010903	3165140846493

WOOD PRECISION, 30 PIECES

- ▶ 10× T 144 DP
- ▶ 10× T 301 BCP
- ▶ 10× T 308 BP



Pack quantity	Order no.	EAN
30 pieces	2607010905	3165140846516

PACKS

Compact storage box

WOOD, 15 PIECES

- ▶ 9× T 144 DP
- ▶ 5× T 101 BF
- ▶ 1× T 144 DHM



Pack quantity	Order no.	EAN
15 pieces	2607011436	3165140997744

WOOD AND METAL, 15 PIECES

- ▶ 6× T 144 DP
- ▶ 5× T 101 BF
- ▶ 3× T 121 BF
- ▶ 1× T 144 DHM



Pack quantity	Order no.	EAN
15 pieces	2607011437	3165140997751

MULTI MATERIAL, 15 PIECES

- ▶ 4× T 144 DP
- ▶ 4× T 101 BF
- ▶ 3× T 121 BF
- ▶ 3× T 345 XF
- ▶ 1× T 367 XHM



Pack quantity	Order no.	EAN
15 pieces	2607011438	3165140997768

SETS

ROBUST LINE

Robust storage box

WOOD EXPERT, 10 PIECES

- ▶ T 101 AO
- ▶ T 101 B
- ▶ T 101 BR
- ▶ T 101 AOF
- ▶ T 101 BF
- ▶ T 101 BRF
- ▶ T 244 D
- ▶ T 144 D
- ▶ T 144 DF
- ▶ T 144 DP

Pack quantity	Order no.	EAN
10 pieces	2607 010 540	3 165 140 446 242



WOOD AND METAL, 10 PIECES

- ▶ T 244 D
- ▶ T 144 D
- ▶ T 101 AO
- ▶ T 101 B
- ▶ T 101 AOF
- ▶ T 101 BF
- ▶ T 118 EOF
- ▶ T 118 AF
- ▶ T 118 BF
- ▶ T 123 X

Pack quantity	Order no.	EAN
10 pieces	2607 010 542	3 165 140 446 266



METAL EXPERT, 10 PIECES

- ▶ T 118 G
- ▶ T 118 A
- ▶ T 118 B
- ▶ T 118 EOF
- ▶ T 118 AF
- ▶ T 118 BF
- ▶ T 118 GFS
- ▶ T 227 D
- ▶ T 127 D
- ▶ T 123 XF

Pack quantity	Order no.	EAN
10 pieces	2607 010 541	3 165 140 446 259



SETS

BLISTER

WOOD, 10 PIECES

- | | |
|-----------|-----------|
| ▶ T 119BO | ▶ T 144 D |
| ▶ T 119B | ▶ T 101AO |
| ▶ T 111C | ▶ T 101B |
| ▶ T 244D | ▶ T 101B |
| ▶ T 144D | ▶ T 101D |

Pack quantity	Order no.	EAN
10 pieces	2607011169	3165140913409



WOOD AND METAL, 10 PIECES

- | | |
|-----------|-----------|
| ▶ T 119BO | ▶ T 101AO |
| ▶ T 119B | ▶ T 101B |
| ▶ T 111C | ▶ T 118A |
| ▶ T 244D | ▶ T 118B |
| ▶ T 144D | ▶ T 127 D |

Pack quantity	Order no.	EAN
10 pieces	2607011170	3165140913416



ALL IN ONE, 10 PIECES

- | | |
|-----------|------------|
| ▶ T 244D | ▶ T 118A |
| ▶ T 144D | ▶ T 118B |
| ▶ T 101AO | ▶ T 127 D |
| ▶ T 101B | ▶ T 118GFS |
| ▶ T 101BF | ▶ T 102 H |

Pack quantity	Order no.	EAN
10 pieces	2607011171	3165140913423



PROGRESSOR, 3 PIECES

- ▶ T 123 XF
- ▶ T 234 X
- ▶ T 345 XF



Pack quantity	Order no.	EAN
3 pieces	2 607 010 515	3 165 140 198 868

LAMINATE, 3 PIECES

- ▶ T 101 BIF
- ▶ T 101 BIF
- ▶ T 101 AOF



Pack quantity	Order no.	EAN
3 pieces	2 608 636 429	3 165 140 393 393

SYSTEM ACCESSORIES

CHIPGUARD FOR JIGSAWS

Compatible with GST 14.4 V; GST 18 V;
GST 75 BE; GST 80 Professional; PST 650;
PST 650 L; PST 680 E; PST 680 EL; PST 700 PE;
PST 800 PEL; PST 900 PEL; PST 1000 CE

Pack quantity	Order no.	EAN
5 pieces	2607010079	3165140006651

Compatible with GST 120 BCE; GST 120 E;
GST 135 BCE; GST 135 CE Professional

Pack quantity	Order no.	EAN
5 pieces	2607010305	3165140356732

Compatible with GST 150 BCE;
GST 150 CE Professional

Pack quantity	Order no.	EAN
5 pieces	2601016096	3165140516297



UNIVERSAL CUTTING OILS

Using the universal cutting oil increases the performance lifetime in metal applications

Pack quantity	Order no.	EAN
1 piece	2607001409	3165140271240



DUST EXTRACTION

Compatible with GST 100 BCE;
GST 135 BCE; GST 140 BCE; GST 150 BCE;
GST 150 CE Professional


Pack quantity	Order no.	EAN
1 piece	2605510294	3165140516280



Compatible with GST 14,4 V-LI; GST 18 V-LI;
GST 140 BCE; GST 140 CE Professional

Pack quantity	Order no.	EAN
1 piece	2605510301	3165140605816





Robert Bosch Limited

Power Tools Division
PO Box 98, Uxbridge
Middlesex, UB9 5HN
UNITED KINGDOM

www.boschpowertools.co.uk

6 035 951 577 – en – PT-AC/MKB1 – Printed by Scintilla AG, Luterbachstrasse 10, 4528 Zuchwil, SWITZERLAND.
Subject to technical changes. Any liability for printing errors is excluded.