



# — PRODUCT DATA SHEET

## iF2R Mini-Worklight 200 (Box)



iF2R

## PRODUCT DESCRIPTION

A work light can actually be that small! The mini version of our floodlight series provides convenient lighting for tight spaces or for illuminating small areas. Just like its big brother, the iF2R can be positioned in different ways with the base, hook and magnet. The wide floodlight lights up the job site with an output of 200 lumen<sup>1</sup>. And the iF2R is also equipped with a small spotlight to use as a flashlight.

- Mini work light with floodlight plus spotlight
- Adjustable base, magnet and hook for mounting and positioning flexibility
- Easy to charge via tough magnetic charge system
- Small and handy
- Three dimmer settings



**7**  
**YEAR**  
**WARRANTY<sup>4</sup>**

### TECHNICAL DATA

Width [mm]	115
Depth [mm]	48
Height [mm]	21
Weight incl. batteries [g]	88
Focus function	No
Primary material	ABS
Secondary material	Other plastics
Cartridge	No

### POWER SUPPLY

Power source type	Rechargeable battery
Battery quantity	1
Battery type	Li-ion
Battery replaceable	No
Total battery voltage [V]	3.7
Total battery capacity [mAh]	1600
Total battery energy <sup>2</sup> [Wh]	5.9
Rechargeable	Yes
Charging time <sup>5</sup> [min]	180
Energy status indicator	Battery Indicator, Charge Indicator

### FURTHER SPECIFICATIONS

IP class	IP54
Drop test (drop height) [m]	1
Working temperature range [°C]	-10 to +40

### LIGHT FUNCTIONS

Power, Low Power

### LIGHT SOURCE

	Flood	Spot
Amount LEDs	1	1
LED type	COB LED	Power LED
Colour temperature [K]	5400 to 6600	5400 to 6600
Colour rendering index (CRI)	80	70

### LIGHT VALUES - Flood

	Boost	Power	Mid Power	Low Power
Light output <sup>1</sup> [lm]		200		100
Run time <sup>1</sup> [h]		3		6

### LIGHT VALUES - Spot

	Boost	Power	Mid Power	Low Power
Light output <sup>1</sup> [lm]		75		
Run time <sup>1</sup> [h]		4		

### SWITCH

Switch

### FEATURES

Transportation lock

### TECHNOLOGIES

Magnetic Charge System

# iF2R

## PACKAGING AND LOGISTICS



### PACKAGING INFORMATION

Type of packaging	Box
Supplied with	Magnetic charging cable
Item No.	502170
Customs tariff number	85131000
Color	black
<b>RRP ex / inc vat (£)</b>	<b>£49.99 / £59.99</b>
<b>RRP EURO ex / incl vat (€)</b>	<b>€55.08 / €67.75</b>

### SINGLE PACKAGE

Dimensions W x H x D [cm]	5 x 16.6 x 3.2
GTIN-13	4058205020206

### INNER CARTON

Unit	6
Dimensions W x D x H [cm]	20.5 x 5.4 x 17.5
GTIN-13	4058205020213

### EXPORT CARTON

Unit	60
Dimensions W x D x H [cm]	38.5 x 30.5 x 25
GTIN-13	4058205020220

iF2R

## ACCESORIES

PRODUCT CATEGORY	ITEM NUMBER	PRODUCT NAME
Charger / Cable	0380	USB Car Charger

# iF2R

## PRODUCT SERIES

### The Ledlenser i-Series Work lights & spotlights

Powerful performance! Ready whenever you need to illuminate the darkness of your workshop or construction site: the Ledlenser i-Series work lights and spotlights - durable multi-purpose lights for true professionals! Whether you use a single spotlight or floodlight with wide coverage, with these professional lights you always have the right type of light at your fingertips. Compact, powerful and rechargeable - each model impresses during everyday use.

## FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurements according to ANSI FL1 on the respective setting. Average values, in some cases, deviations by +/- 15 % may occur due to technical reasons. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting and to battery duration (hours/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If no setting is explicitly indicated, measurement is based on "energy saving mode."

2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.

4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the products of the "Solidline" series, Ledlenser K1 and Ledlenser K2. The warranty does not apply to defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 - 7, 42699 Solingen, Germany. More information: [ledlenser.com/warranty](http://ledlenser.com/warranty)

5) Charging time varies by hardware used.