

249 SERIES FOR 3/8" MOUNTING HOLE

PART NUMBER*	COLOR	VOLTAGE	mA	SERIES	
				OHMS	FIG
249-7841-1431-574	RED	105-125 AC-DC	0.7	100K	1
249-7841-1433-574	AMBER	105-125 AC-DC	0.7	100K	1
249-7841-1437-574	CLEAR	105-125 AC-DC	0.7	100K	1
249-7866-1431-514	RED	110-125 AC-DC	1.9	22K	1
249-7866-1433-514	AMBER	110-125 AC-DC	1.9	22K	1
249-7866-1437-514	CLEAR	110-125 AC-DC	1.9	22K	1

Material & Finish: Housing - Black Anodized Aluminum. Cap - High Impact Plastic



***PART NUMBER ORDERING CODE**

249 - 7841 - xx3x - 574
249 - 7866 - xx3x - 514

Series: 249
 Lens Shape: 14 - Fig 1 = Cylindrical, 09 - Fig 2 = Stovepipe

507 SERIES CARTRIDGES FOR HOLDERS & CLIPS • 25,000 LIFE HOURS

PART NUMBER*	COLOR	VOLTAGE	mA	SERIES	
				OHMS	FIG
507-4537-1431-640	RED	105-125 AC-DC	0.3	100K	3
507-4537-1433-640	AMBER	105-125 AC-DC	0.3	100K	3
507-4537-1435-640	WHITE	105-125 AC-DC	0.3	100K	3
507-4537-1437-640	CLEAR	105-125 AC-DC	0.3	100K	3
507-4538-1431-630	RED	110-125 AC-DC	1.2	47K	3
507-4538-1433-630	AMBER	110-125 AC-DC	1.2	47K	3
507-4538-1435-630	WHITE	110-125 AC-DC	1.2	47K	3
507-4538-1437-630	CLEAR	110-125 AC-DC	1.2	47K	3

Material & Finish: Housing - Clear Anodized Aluminum. Cap - High Impact Plastic



***PART NUMBER ORDERING CODE**


507 - 4537 - xx3x - 640
507 - 4538 - xx3x - 630

Series: 507
 Lens Shape: 14 - Fig 3 = Cylindrical, 09 - Fig 4 = Stovepipe

250 & 508 SERIES HOLDERS FOR 3/8" MOUNTING HOLE



250-8745-14-504



508-8745-504

***PART NUMBER ORDERING CODE**

250 - xx45 - 14 - 504
508 - xx45 - 504

Series: 250/508
 Terminal Type: 87 = Turret Terminals, 74 = Solder Blade (Not Shown), 75 = Solder Cups (Not Shown)

250 Series Caps for use with 507 cylindrical cartridges. (Fig. 3)


CAP PART NO.	COLOR	FIG
250-3531-500	RED	5
250-3533-500	AMBER	5
250-3535-500	WHITE	5
250-3537-500	CLEAR	5




Material & Finish: Holders - Black Anodized Aluminum, Cap - Polycarbonate Fig. 5, High Impact Plastic Fig. 6, Cartridge - Clear Anodized Aluminum

250 Series Caps for use with 507 stovepipe cartridges. (Fig. 4)

CAP PART NO.	COLOR	FIG
250-1631-500	RED	6
250-1633-500	AMBER	6
250-1635-500	WHITE	6
250-1637-500	CLEAR	6



515 SERIES CONNECTORS & SPEED CLIPS FOR 9/32" MOUNTING HOLE



Green and Blue Lens Caps Not Available for Neon Indicators
 Dimensions in mm [inches]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[507-4538-1531-630](#) [507-4537-1531-640](#) [507-4537-0937-640](#) [507-4538-1433-610](#) [507-4537-0931-640](#) [507-4538-1435-610](#) [507-4538-0931-610](#) [507-4538-0936-630](#) [507-4538-1535-630](#) [507-4537-1533-670](#) [507-4538-0933-610](#) [507-4537-1531-670](#) [507-4538-1435-630](#) [507-4537-0937-670](#) [507-4538-1533-630](#) [507-4538-1531-610](#) [507-4537-1437-640](#) [507-4538-0931-630](#) [507-4538-0937-610](#) [507-4538-1533-610](#) [507-4538-1436-630](#) [507-4538-1437-630](#) [507-4538-0933-630](#) [507-4538-1535-610](#) [507-4538-0935-610](#) [507-4538-1431-610](#) [507-4538-0935-630](#) [507-4538-1431-630](#) [507-4538-1433-630](#) [507-4537-1537-640](#) [507-4537-1437-670](#) [507-4537-1537-670](#) [507-4537-1431-670](#) [507-4537-1431-640](#) [507-4537-0931-670](#) [507-4537-1431-570](#) [507-4537-1433-670](#) [507-4537-1433-640](#) [507-4537-1533-640](#) [507-4537-1435-640](#) [507-4537-1535-640](#) [507-4537-1535-670](#) [507-4537-1435-670](#) [507-4538-1536-610](#) [507-4537-0935-640](#) [507-4538-1437-610](#) [507-4538-1537-610](#) [507-4538-1537-630](#) [507-4537-0933-640](#) [507-4537-0933-670](#) [507-4537-0931-640F](#) [507-4537-0933-640F](#) [507-4537-0933-670F](#) [507-4537-0935-640F](#) [507-4537-0937-640F](#) [507-4537-0937-670F](#) [507-4537-1431-570F](#) [507-4537-1431-640F](#) [507-4537-1431-670F](#) [507-4537-1433-640F](#) [507-4537-1435-640F](#) [507-4537-1435-670F](#) [507-4537-1437-640F](#) [507-4537-1437-670F](#) [507-4537-1531-640F](#) [507-4537-1531-670F](#) [507-4537-1533-640F](#) [507-4537-1533-670F](#) [507-4537-1535-640F](#) [507-4537-1535-670F](#) [507-4537-1537-640F](#) [507-4537-1537-670F](#) [507-4538-0931-610F](#) [507-4538-0931-630F](#) [507-4538-0933-610F](#) [507-4538-0933-630F](#) [507-4538-0935-610F](#) [507-4538-0935-630F](#) [507-4538-0936-630F](#) [507-4538-0937-610F](#) [507-4538-1431-610F](#) [507-4538-1433-610F](#) [507-4538-1435-610F](#) [507-4538-1435-630F](#) [507-4538-1436-630F](#) [507-4538-1437-610F](#) [507-4538-1437-630F](#) [507-4538-1531-610F](#) [507-4538-1531-630F](#) [507-4538-1533-610F](#) [507-4538-1533-630F](#) [507-4538-1535-610F](#) [507-4538-1535-630F](#) [507-4538-1536-610F](#) [507-4538-1537-610F](#) [507-4538-1537-630F](#)