


plug
SEA-3GS-M8-S
 Part number: 192009



Data sheet

Feature	Value
Based on the standard	EN 61076-2-101 EN 61984
Mounting type	with threaded sleeve
Assembly position	Any
Product weight	11 g
Electrical connection	M8x1 3-pin Straight plug / screw terminal
Operating voltage range DC	<= 60 V
Operating voltage range AC	<= 60 V
Acceptable current load at 40°C	3 A
Surge strength	1.5 kV
Cable gland connection	Pg7
Permissible cable diameter	2.5 ... 5 mm
Terminal cross-section	0.14 ... 0.5 mm ²
Protection class	IP65
Ambient temperature	-40 ... 85 °C
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material housing	PA
Housing colour	Black
Material of union nut	Brass Chromed-plated Nickel plated
Material electrical contact	Brass Gold plated