


distributor block

FR-8-1/4

Part number: 2078

FESTO



Data sheet

Feature	Value
Nominal size	11.5 mm
Assembly position	Any
Operating pressure complete temperature range	0 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Ambient temperature	-10 ... 60 °C
Product weight	230 g
Number of outputs	8
Number of supply lines	1
Pneumatic connection, port 1	Female thread G1/2
Pneumatic connection, port 2	Female thread 1/4
Materials note	Conforms to RoHS
Material housing	Aluminium die cast