


## 10001300 DATASHEET



PART No.	BALL SIZE (mm)	WEIGHT (kgs)	MAXIMUM DIAMETER (mm)	WORKING HEIGHT OF BALL (mm)	BALL EXPOSURE ABOVE OUTER RING (mm)	FLANGE THICKNESS (mm)	HOLE SIZE (mm)	HOLE CENTRES PCD (mm)
10001300	Ø25.4	0.175	Ø73.0	14.2	6.3	3.5	Ø5.1	55.6 +/- 0.2

## MAXIMUM DYNAMIC LOADING

Type 13 with carbon steel load ball 55kgs ball up, 25kgs ball down

## MATERIALS

Body - Carbon steel with zinc plated finish Load ball – Carbon steel with hardness of 60 – 62HRC self colour finish Small balls – Chrome steel with hardness of 60 – 65HRC self colour finish Seal – Woollen felt

## **KEY FEATURES**

Low profile x2 fixing holes in flange for securing unit Single dirt exit hole in base of unit Operating temperature 70°C continuous to 100°C intermittent