

RCBO personal protection socket strip 4-fold with switch

Item-no.: 0250x00042301 (1,5 m cord)



Robust plastic, grey

Built-in sockets (90° rotated), round

Extra large space in between sockets 64 mm

1,5 m power cord and angle plug

Personal protection through RCD (30 mA)

Circuit breaker 16A





Expanded contact protection by using a shutter

End caps with mounting possibility



RCBO personal protection socket strip 4-fold with switch

Technical data

3.600 W Power	230 V ~ (+/- 10%) / 50 Hz Rated voltage	16 A Rated current
Power cord: H05VV-F 3G 1,5 mm ² Plug: CEE 7/7 plug, angular type EF Sockets: earthing contact type F Switch: 2-pole, illuminated Consumption switch: < 0,5 W Personal Protection: RCD (30 mA) Circuit breaker: 16A Safety class: IP20		  
 <p>(similar illustration)</p>		
Item-no. 0250x00042301 (1,5 m) EAN 401209600141 6 PU 20		462 x 74 x 47 mm Dimensions (L x W x H) 454 mm Fixing dimension