

# IT master-slave PRO socket strip 5-fold

Item-no.: 0214x00058341 (1,5 m cord)



Robust plastic, grey

Built-in sockets (90° rotated), round


1,5 m power cord and angle plug (optional with 3 m or 5 m power cord)

Automatic electronic switching M/S with precisely adjustable switching threshold

Optical function display for M/S function





Expanded contact protection by using a shutter

End caps with mounting possibility (19")



## IT master-slave PRO socket strip 6-fold

### Technical data

3.600 W Power	230 V ~ (+/- 10%) / 50 Hz Rated voltage	16 A Rated current
Power Cord: H05VV-F 3G 1,5 mm <sup>2</sup> Plug: CEE 7/7 plug Type EF, angled Sockets: earthing contact Type F Precise switching threshold: 7-100 W (master) Consumption: < 0,6 W Safety class: IP20		  
 <p>(similar illustration)</p>		
Item-no. 0214x00058341 (1,5 m cord)    EAN 401209600748 7    PU 10		484 x 74 x 47 mm Dimensions (L x W x H) 458 mm Fixing dimension