

USB multi-charger 6-port 6,3 A with 2 sockets type F

Item-no.: 0601x0a02203303 (3 m cord)



Noble, transparent anodized aluminum case, matt

3 USB double-ports with max. 2,1A each

Enables fast charging of up to 8 devices at the same time

Especially suitable for smart phones and tablets from Samsung, Apple, Huawei, HTC, LG, Sony, etc.


3 m power cord with angle-plug, for flexible positioning

Built-in sockets (90° rotated), round

Expanded contact protection by using a shutter





2-pole switch, no stand-by consumption

End caps with mounting possibility



USB multi-charger 6-port 6,3 A with 2 schuko sockets

Technical data

3.600 W Power	230 V ~ (+/- 10%) / 50 Hz Rated voltage	16 A Rated current
Power cord: H05VV-F 3G 1,5 mm ² Plug: CEE 7/7 plug, angled type EF USB: 2-fold charger, AC voltage range: 100-240 V AC, 50/60Hz Output voltage: 5V DC Charging current: max. 2,1A (per charger) Compatible: Apple, Android, Google, etc. Sockets: earthing contact Type F Switch: 2-pole, unlit, black Safety class: IP20		  
 <p>(similar illustration)</p>		
Item-no. 0601x0a02203303 (3m cord) EAN 4012096007425 PU 10		330x65x44 mm Dimensions (L x W x H) 324 mm Fixing dimensions (X)