



**SPECIFICATIONS:**

Current Rating: 1A AC,DC  
 Voltage Rating: 30V AC,DC  
 Temperature Range: -40°C ~ +105°C  
 Contact Resistance: 30mΩ Max.  
 Insulation Resistance: 100MΩ Min.  
 Withstanding Voltage: 200V AC/minute  
 Material: LCP , UL94V-0(Natural)

**Ordering Information & Dimensions**

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	0.80	2.40	12P	8.80	10.40
3P	1.60	3.20	13P	9.60	11.20
4P	2.40	4.00	14P	10.40	12.00
5P	3.20	4.80	15P	11.20	12.80
6P	4.00	5.60	16P	12.00	13.60
7P	4.80	6.40	17P	12.80	14.40
8P	5.60	7.20	18P	13.60	15.20
9P	6.40	8.00	19P	14.40	16.00
10P	7.20	8.80	20P	15.20	16.80
11P	8.00	9.60			



CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	10:1	1 of 1

Draw BY:	Approved :
Jack Yin	GONGYB

Title :  
**0.80mm PITCH Housing**

General Tolerance

x.x≤0.25	ANGLE±
x.xx≤0.20	
x.xxx≤0.15	

DRAW NO : **A0801H-XP**      REV A0

A0	NEW RELEASE	2015.03.23
REV	DESCRIPTION	DATE