

Search within category **GO**

UGB2/0-414-18



Universal ground bar accepts #14 – #4 AWG wire in 18 wire ports and up to a 2/0 AWG main equipment grounding conductor with a compression or mechanical connector, 11.64" (295.7mm) length, 0.62" (15.7mm) width, 0.48" (12.2mm) height.

BUY NOW

DESIGN / INSTALL

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Height (In.)	0.48			
Height (mm)	12.2			
Length (In.)	11.64			
Length (mm)	295.7			
Width (In.)	0.62			
Width (mm)	15.7			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			