



Combination spanner, offset, 1952M

Combination spanner, offset in Metric sizes.

DIN 3113 / ISO 3318 / ISO 7738

Finish: nickel and chrome-plated. Sizes up to 36 mm, fine polished.






Material: VANADIUM-EXTRA.

Open-end angle 15°, box end 10° offset, equal openings at both ends.

Dynamic-Drive-Profile up to 36 mm.

SB = Retail packed on a plastic info card.



				L mm	a2xa1 mm	b2xb1 mm	
1952M-6	1057176	10	6	95	4.5x3.7	9.5x14.0	15
1952M-7	1057183	10	7	105	5.0x3.8	11.0x16.0	19
1952M-8	1057190	10	8	115	5.5x4.2	12.2x18.0	23
1952M-9	1057206	10	9	125	6.0x4.5	13.2x20.0	30
1952M-10	1057213	10	10	135	6.5x4.8	14.6x22.0	40
1952M-11	1057220	10	11	145	7.0x5.0	16.2x24.0	49
1952M-12	1057237	10	12	155	7.5x5.2	17.5x26.5	61
1952M-13	1057244	10	13	170	8.0x5.6	19.0x28.5	68
1952M-14	1057251	10	14	185	8.5x6.0	20.0x31.0	80
1952M-15	1057268	10	15	185	9.0x6.2	21.5x33.0	100
1952M-16	1057275	10	16	205	9.8x6.5	23.0x35.0	110
1952M-17	1057282	10	17	220	10.6x7.0	24.5x37.0	135
1952M-18	1057299	10	18	230	11.4x7.2	26.0x39.0	155
1952M-19	1057305	10	19	245	12.2x7.5	27.0x41.5	195
1952M-20	1057312	10	20	265	13.0x8.0	28.5x43.5	217
1952M-21	1057329	10	21	265	13.0x8.0	30.0x43.5	240
1952M-22	1057336	5	22	265	13.5x8.5	32.0x48.0	297
1952M-23	1057343	5	23	300	13.5x8.5	33.0x48.0	290
1952M-24	1057350	5	24	300	14.5x9.0	34.5x52.0	375
1952M-25	1057367	5	25	330	15.5x9.5	36.0x54.5	400
1952M-26	1057374	5	26	330	15.5x9.5	36.5x54.5	400
1952M-27	1057381	5	27	330	16.5x10.0	38.5x59.0	590
1952M-28	1057398	1	28	370	17.0x10.0	40.0x61.0	700
1952M-29	1325763	1	29	370	17.0x10.0	40.0x61.0	690
1952M-30	1057404	1	30	370	18.0x10.7	42.5x64.0	727
1952M-32	1057411	1	32	390	19.0x11.5	45.5x68.0	745
1952M-34	1838553	1	34	415	20.0x12.0	48.0x72.0	800
1952M-36	1057428	1	36	435	21.0x13.5	52.0x78.0	1230
1952M-41	1057435	1	41	495	24.4x14.4	61.5x86.7	1350

1952M-46	1840105	1	46	520	25.4x15.4	67.0x93.6	1750
1952M-50	1840112	1	50	560	26.2x16.3	74.9x104.4	2200
1952M-55	1840129	1	55	570	28.6x19.1	82.7x113.3	3200
1952M-60	1840136	1	60	660	31.0x20.0	90.0x123.0	3600
1952M-65	0135226	1	65	710	33x22	98x133	4500
1952M-70	0135301	1	70	760	35x24	105x143	5600
1952M-75	0135325	1	75	810	38x26	110x153	6780
1952M-80	0135509	1	80	860	41x28	119x163	8780