


Product sheet **Subminiature connectors**

Female socket, solder, front fastened 09 0408 80 03 Area M9 connectors IP 67 serie 712/702 Article number

illustration



Contact Arrangement



3

Installation instructions / Mounting cutout



Technical data

Common values

Female socket Connector Design Screw-locking Connector locking system solder Termination 0,25 mm² Wire gauge (mm) 24 Wire gauge (AWG) Max. Cable outlet +85 °C Upper temperature -40 °C Lower temperature

Electrical values

Mechanical operation

125 V Rated voltage 1500 V Rated impulse voltage 1 Pollution degree Ш Overvoltage category Ш Material group 4 A Rated current (40°C) ≤ 3 mΩ Volume resistivity shieldable EMV compliance IP 67 Degree of protection >500 mating cycles

Material

CuSn (bronce) Material of contact Au (gold) Contact plating PA (UL 94 V-0) Material of contact body CUZn (brass nickel plated) Material of housing

Cable data

material housing insulation single lead single lead structure conductor resistance

Contacts 3, Female socket, solder, front fastened

