

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet




tasker® RG 59 Flex -Coaxial Cable 75 Ω



A	B	C	D
---	---	---	---

- CATEGORY** Coaxial cable 75 Ω (See Video Catalogue)
- A:** **PVC Sheath.** – available in different color.
 Outer cable Diam. Ø 6,10 (±0,10) mm.
- B:** Shielding in O.F.C. red copper braid covering 90% .
- C:** Core Insulation with transparent PE – Diam. Ø 3,70 (±0,10) mm.
- D:** Stranded O.F.C. red copper formation 7x0,20 mm.
 Nom. Cross section 1x0,22 mm².

MARKING **tasker® RG59 FLEX 75Ω BROADCAST VIDEO CABLE**

CUSTOM This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	75 Ω/Km ± 5%
Capacity Core/Shield	67 pF/mt
Velocity of Propagation	66%
Impedance	75 Ω ± 3%
Max Rated Voltage	2.000 V
Operative Temperature	-15/+70°C

Attenuation dB/100 mt.

50 MHz	7,4
100 MHz	10,7
200 MHz	15,7
400 MHz	22,7
800 MHz	33,6
1000 MHz	38,0

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 08.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		