



Porcelain Connectors

157 - 2 and 3 pole, conductor size without wire protector 6 mm²

Approvals		
Click for Approvals (PDF)		
Nominal cross-section	mm ²	2,5
Voltage rating	V	450

Technical data

Connection	screw conductor size 0.5 - 6.0 mm ²
Fixing	by screw or rivet size Ø 3.2 mm
Mouldings	porcelain C 111 EN 60672 glazed porcelain, white, except lower surface continuous working temperature 1000 °C
Contacts	brass, plated continuous working temperature: 350 °C
Screws	M3: ⌀ max. 0.5 Nm steel, zinc plated, chromed captive screws
Current rating	to EN 60598: 16 A at T 100 °C to EN 60998: 24 A at T 100 °C
Stripping length	7 - 7.5 mm

Upon request

printing, different screws; further product variants [here](#)

Variants

157 DS	2 and 3 pole, conductor size with wire protector 2.5 mm ²
157 MDS	2 and 3 pole, conductor size with wire protector and center stop 2.5 mm ²

Order info

Description	Item	Order No.	PU	
2 pole	157/ 2	412202	400	›
3 pole	157/ 3	412203	250	›