

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



Halogen Free

Firestop®

tasker® RG 58 PUR Coaxial 50Ω Mil. C 17 F Standard Cable



A		B		C		D
---	--	---	--	---	--	---

CATEGORY Coaxial cable 50 Ω (See Video Catalogue)

- A:** Black Polyurethane (**PUR**) sheath - Outer Cable Diam. Ø 5,00 (±0,20) mm.
- B:** Shielding O.F.C. tinned copper braid covering 98% .
- C:** Core Insulation with transparent compact PE – Diam. Ø 3,00 mm (±0,20) mm.
- D:** O.F.C. tinned copper stranded formation, 19x0,18 mm.
Nom. Cross section 1x0,48 mm² (50Ω).

**MARKING
CUSTOM**

tasker® RG58 PUR 50 Ω Mil. C/17F OUTDOOR USE CABLE MADE IN ITALY
 This product is also available in **L.S.Z.H., PE, PVC**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	40 Ω/Km ± 5%
Capacity Core/Shield	100 pF/mt
Velocity of Propagation	66%
Impedance	50 Ω ± 3%
Max Rated Voltage	2.000 V
Operative Temperature	-40/+80°C

Attenuation dB/100 mt.

50 MHz	9,7
100 MHz	13,9
200 MHz	20,4
400 MHz	30,0
800 MHz	45,1
1000 MHz	51,8

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. A / 12.01.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		