

MILAN S.r.l. a socio unico

Head Office – Export department:  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it

## Technical Datasheet ✔ **RoHS<sub>3</sub>**

### **tasker® TSK1028 – 2x0,35 mm<sup>2</sup> - ZERO LOSS**

### **Balanced Microphone Cable with Conductive Tape**



A	B	C	D	E
---	---	---	---	---

**CATEGORY**  
**APPLICATIONS**

Balanced Microphone Cable ( See Audio Catalogue)  
 Long distances Audio connections

- A:** Black soft **PVC** sheath. Outer Diam. Ø: 6,30 (±0,20) mm.
- B:** Braided Shield in O.F.C. tinned copper, covering 90%.
- C:** Special Active Carbon Screen tape.
- D:** Core Insulation with compact Transparent PE.  
Diam. Ø 1,70 (±0,20) mm.
- E:** One conductor in O.F.C. red copper and one in O.F.C. tinned copper –  
formation 11x0,20 mm. Nom. Cross section 2x0,35 mm<sup>2</sup>.


**MARKING**

**tasker® TSK 1028 2x0,35 mm<sup>2</sup> - O.F.C.- ZERO LOSS - Low Capacitance –**  
 Active Carbon Screen - Audio Microphone Cable Made in Italy

**CUSTOM**  
**PRODUCTION**

This product may be custom produced also in **LSZH, PE, PUR**,  
 with or without Metallic Armor.

**Attenuation Test – Start 9 KHz – Stop 25 KHz**



**Cable Properties**

<b>Conductor Resistance</b>	58 Ω/Km
<b>Capacity Core/Core</b>	55 pF/m
<b>Capacity Core/Shield</b>	90 pF/m
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<input checked="" type="checkbox"/>	Fixed	Fissa	<b>INFORMATION</b>	<input checked="" type="checkbox"/>	RoHS3 Compliant
<b>Impiego</b>		Outdoor Limited	Esterno Limitato	<b>Posa</b>	<input checked="" type="checkbox"/>	Restricted Mobile	Mobile Limitata	<b>Informazioni</b>	<input checked="" type="checkbox"/>	Ver. A / 16.05.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			