

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it



Technical Datasheet

tasker® C277 – 2x4,00 mm²

Flexible Double Density Sheath Speaker Cable



| | | | |
|---|---|---|---|
| A | B | C | D |
|---|---|---|---|

CATEGORY **Flexible Speaker Cable** (See Audio Catalogue)

- A:** First Soft **PVC** Sheath. - available in different color.
Outer cable Diam. Ø 10,80 (±0,20) mm.
- B:** Second Soft **PVC** Sheath with different density.
- C:** Core Insulation with a Third PVC Sheath, colored one Red and one Black.
Diam. Ø 4,20 (±0,20) mm.
- D:** O.F.C. red copper formation 120x0,20 mm.
Nom. Cross section 2x4,00 mm².

MARKING
CUSTOM
PRODUCTION

tasker® C277 2x4.00 - 11 AWG – O.F.C. Loudspeaker Cable – Italy
 This product may be custom produced also in **L.S.Z.H.** polymer, **PE, PUR**, with or without Metallic Armor.

Cable Properties

| | |
|------------------------------|-----------|
| Conductor Resistance | 4,31 Ω/Km |
| Max Rated Voltage | 49 V |
| Operative Temperature | -15/+70°C |

| | | | | | | | | | | |
|----------------|----------|-----------------------|-------------------|---------------------|----------|----------------------|-----------------------|---------------------|----------|-------------------|
| USE | X | Indoor | Interno Edificio | INSTALLATION | X | Fixed | Fissa | INFORMATION | X | RoHS2 Compliant |
| Impiego | X | Outdoor Limited | Esterno Limitato | Posa | X | Flexible Limited | Flessibilità limitata | Informazioni | X | Ver. A / 02.11.15 |
| | | Outdoor Direct Burial | Esterno Interrato | | X | Dynamic (Drag Chain) | Mobile in Catena | | | |
| | | | | | | Dynamic (Torsion) | Mobile in Torsione | | | |