

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HSTT 12 - 48 0 2


COLOR
 BLANK = BLACK 5 = GREEN
 1 = BROWN 6 = BLUE
 2 = RED 10 = WHITE
 3 = ORANGE 45 = YELLOW/GREEN
 4 = YELLOW C = CLEAR

QUANTITY PER CARTON (48 IN ONLY)
 0 = 25pcs.
 5 = 5pcs.
 2 = 2pcs.

LENGTH IN"
 INCHES FEET:
 .5 M=1000
 1 D=500
 48 T=200
 C=100
 L=50
 Q=25

TUBING SIZE - EXPANDED I.D.

TT = THIN WALL
 TTV = THIN WALL VW-1 RATED



PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	RECOVERED WALL In. (mm)
HSTT05	.046 (1.2)	.023 (.6)	.016±.003 (.406±.076)
HSTT06	.063 (1.6)	.031 (.8)	.017±.003 (.432±.076)
HSTT09	.093 (2.4)	.046 (1.2)	.020±.003 (.508±.076)
HSTT12	.125 (3.2)	.062 (1.6)	.020±.003 (.508±.076)
HSTT19	.187 (4.8)	.093 (2.4)	.020±.003 (.508±.076)
HSTT25	.250 (6.4)	.125 (3.2)	.025±.003 (.635±.076)
HSTT38	.375 (9.5)	.187 (4.8)	.025±.003 (.635±.076)
HSTT50	.500 (12.7)	.250 (6.4)	.025±.003 (.635±.076)
HSTT75	.750 (19.1)	.375 (9.5)	.030±.003 (.762±.076)
HSTT100	1.000 (25.4)	.500 (12.7)	.035±.005 (.889±.127)
HSTT150	1.500 (38.1)	.750 (19.1)	.040±.006 (1.016±.152)
HSTT200	2.000 (50.8)	1.000 (25.4)	.045±.007 (1.143±.178)
HSTT300	3.000 (76.2)	1.500 (38.1)	.050±.008 (1.270±.203)
HSTT400	4.000 (101.6)	2.000 (50.8)	.055±.009 (1.397±.229)

△ B

△ B

NOTES:

- SHRINK RATIO: 2:1
- MATERIAL: CROSSLINKED POLYOLEFIN
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"
- REELS OF PRODUCT ARE ALLOWED TO HAVE SPLICES.

△ E

PACK CODE	M	D	T	C	L	Q
ALLOWED SPLICES	4	3	2	1	1	0

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	5/15/13	LEF	VJS	△ ADDED NOTE #4 ALLOWED SPLICES PER REEL LENGTH	GB0239KH	3	RAMI	
2	2/21/12	LEF		△ ADDED "CUSTOMER DRAWING" TO TITLE BLK △ REMOVED ALL TOLERANCES IN TITLE BLK	GB0239KH	2	RAMI	
1	10/5/11	LEF		△ ADD COLORS 1 & 3 △ CHANGE METRIC (19.0 TO 19.1)	GB0239KH	1	RAMI	

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597HN_DC_G00239KH_PB_HSTT_03

PANDUIT CORP. TINLEY PARK, ILLINOIS

HSTT THIN WALL HEAT SHRINKABLE TUBING CUSTOMER DRAWING

△ C

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) _____ (.XXX) _____
 (.XX) _____ ANGLES _____

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

△ D

DRAWN BY LGRAVITT MAT'L: SEE NOTES

DATE 5/12/03

CHK'D

SCALE NONE

DRAWING NO. GB0239KH DWG SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[HSTT50-YK1](#) [HSTT12-YK1](#) [HSTT-YK1-45](#) [HSTT100-YK1](#) [HSTT50-48-5](#) [HSTT25-Q](#) [HSTT75-48-5](#) [HSTT25-48-Q](#)
[HSTTV25-48-Q](#) [HSTT09-48-Q10](#) [HSTTV09-48-Q](#) [HSTT-YK1](#) [HSTT75-YK1](#) [HSTT38-YK1](#) [HSTT19-YK1](#) [HSTT05-C](#)
[HSTT06-Y](#) [HSTT12-Y](#) [HSTT19-C](#) [HSTT19-Q](#) [HSTT19-Y](#) [HSTT25-C](#) [HSTT25-D](#) [HSTT25-Y](#) [HSTT38-Y](#) [HSTT50-](#)
[Q](#) [HSTT50-48-Q](#) [HSTT75-Q](#) [HSTT75-Y](#) [HSTT100-C](#) [HSTT100-Y](#) [HSTT05-48-Q2](#) [HSTT12-48-Q2](#) [HSTT38-48-Q2](#)
[HSTT75-C2](#) [HSTT38-C5](#) [HSTT75-C5](#) [HSTT100-48-5-6](#) [HSTT12-48-Q45](#) [HSTT19-C2](#) [HSTT150-48-5C](#) [HSTT05-MC](#)
[HSTT50-48-5-10](#) [HSTT38-48-QC](#) [HSTT25-48-Q10](#) [HSTT25-48-Q5](#) [HSTT38-48-Q5](#) [HSTT38-48-Q10](#) [HSTT50-C2](#)
[HSTT12-48-Q10](#) [HSTTV19-48-Q](#) [HSTT75-48-5-4](#) [HSTTV09-Y](#) [HSTTV06-Y](#) [HSTTV100-48-5](#) [HSTT300-L](#) [HSTT38-](#)
[48-Q45](#) [HSTT05-48-Q5](#) [HSTT50-C4](#) [HSTT25-48-TLC](#) [HSTT50-CC](#) [HSTT09-48-QC](#) [HSTT75-48-CQ](#) [HSTT06-QC](#)
[HSTTV25-D2](#) [HSTT09-CC](#) [HSTT50-T5](#) [HSTTV12-48-TL](#) [HSTTV38-T6](#) [HSTT06-48-Q5](#) [HSTT12-M2](#) [HSTT75-C10](#)
[HSTT05-48-Q10](#) [HSTTV25-D10](#) [HSTTV50-Q](#) [HSTT12-C5](#) [HSTT100-48-5-5](#) [HSTT38-CC](#) [HSTT19-48-Q2](#) [HSTT09-](#)
[C6](#) [HSTT50-48-T](#) [HSTT19-M10](#) [HSTT25-D4](#) [HSTT12-48-Q6](#) [HSTT19-48-TL](#) [HSTTV50-T6](#) [HSTT38-C6](#) [HSTT200-](#)
[L6](#) [HSTT100-C2](#) [HSTT50-T4](#) [HSTTV38-T](#) [HSTT06-48-Q2](#) [HSTT12-M4](#) [HSTT06-C5](#) [HSTT150-C6](#) [HSTT12-M45](#)
[HSTTV05-Q](#) [HSTT200-48-5-6](#) [HSTT05-C2](#) [HSTT100-C10](#)