



SPECIFICATIONS

Performance level	PL2
Filter type	C
Capacitance	1000 pF ± 20%
Working voltage	100 V
Current rating	7,5 A
Insulation resistance	> 1 GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1
10	3
50	12
100	20
500	34
1000	30

PCB layout, component side, thickness 1,6 mm

A				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, angled, 25 poles, turned solder pins, clinch nuts and brackets with board locks	Maßstab/ Scale 1,5:1
				Detail.	08/07/02 CV			
	36283	12/01/12	SD	Insp.	12/01/12 JB			
	EC01003	25/11/09	PK	Stand.				
	09 64 324 7233	M3	HARTING EURL F-95972 Paris				TB 09 64 324 723X	Blatt/ Page 1 / 4
	09 64 324 7232	4-40 UNC-2B						
	Part number	Nut thread						
			Mod.	Dot.	Name			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09643247232](#) [09643247233](#)