
Connector A: SMA Ja Connector B: SMA Ja	•	,		
Body Style	Bulkhead Mount			
	Connector A		Conne	ctor B
Connector Part	Material	Finish	Material	Finish
Body	Brass	Gold	Brass	Gold
Center Contact	BeCu	Gold	BeCu	Gold
Insulator	PTFE	-	PTFE	-
	Material		Finish	
Washer	Brass		Gold	
Nut	Brass		Gold	



FLAT 5.9

SHEET 1 OF 2

REV

Α

## SEE SHEET 1 FOR REVISIONS

## 5 TABLE I


Electrical Data	Detail	
Impedance	50 Ω	
Frequency Range	0 to 18 GHz	
Insulation Resistance	5000 MΩ Min	
Voltage Rating	1000 V RMS	
Contact Resistance	Center: 2.0 mΩ Max Outer: 2.0 mΩ Max	
VSWR	1.25 Max	

## 6 TABLE II

Environmental Data	Detail	
Corrosion (Salt Spray)	MIL-STD-202 Method 101 Test Condition B	
Thermal Shock	MIL-STD-202 Method 107 Test Condition B	
Vibration	MIL-STD-202 Method 204 Test Condition D	
Mechanical Shock	MIL-STD-202 Method 213 Test Condition I	
Temperature Range	-65°C to +165°C	
Environmental Compliance	ROHS	

## 7 TABLE III

Mechanical Data	Detail	
Mounting Type	Panel Mount, Surface Mount, Straight	
Fastening Type	1/4"-36UNS Threaded Coupling	
Recommended Torque	0.57 N.m (5 in.lbs)	
Coupling Nut Retention	60 lbs Min	
Connector Durability	500 Cycles Min	
Weight	4.0 g (0.14 oz)	



REV

Α