
Ordercode: BCC00UP





## EH[ 🗷

$\overline{}$			4.5
-	lectrica	Lconn	naction
_	iculiua	i Guili	IECLIUII

Cable diameter D 6...8 mm

Connection M16x0.75-Female, angled, 8-

Contact shield pole
Shield ring

Number of connectable contacts

System Can be fabricated

Electrical data

Operating voltage Ub 60 VDC / 60 VAC

Rated current (40 °C) 5.0 A

Environmental conditions

Ambient temperature -40...95 °C Protection degree IP67

General data

Approval/Conformity EAC WEEE

Material

Material contact carrierPBTMaterial contactsBronzeMaterial cover nutBrass

Material grip Die-cast zinc

Mechanical data

Connection cross-section 0.14...0.75 mm<sup>2</sup>
Type of wire mounting Solder connections

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Connector view

