

Справочник по полупроводниковым диодам 2

Диод	U _{об} /U _{имп} В/В	I _{пр} /I _{имп} А/А	U _{пр} /I _{пр} В/А	Сд/Уд пф/В (Т нс)	I _о (25) /I _{ом} мА/мА	F _{max} кГц	P/P _т Вт/Вт
КД201А	100/	5/15	1.0/ 5		/3	1.1	
КД201Б	100/	10/15	1.0/10		/3	1.1	
КД201В	200/	5/15	1.0/ 5		/3	1.1	
КД201Г	200/	10/15	1.0/10		/3	1.1	
КД202А	35/50	5/9	0.9/ 5		/1	1.2	
КД202Б	35/50	3.5/9	0.9/ 3.5		/1	1.2	
КД202В	70/100	5/9	0.9/ 5		/1	1.2	
КД202Г	70/100	3.5/9	0.9/ 3.5		/1	1.2	
КД202Д	140/200	5/9	0.9/ 5		/1	1.2	
КД202Е	140/200	3.5/9	0.9/ 3.5		/1	1.2	
КД202Ж	210/300	5/9	0.9/ 5		/1	1.2	
КД202И	210/300	3.5/9	0.9/ 3.5		/1	1.2	
КД202К	280/400	5/9	0.9/ 5		/1	1.2	
КД202Л	280/400	3.5/9	0.9/ 3.5		/1	1.2	
КД202М	350/500	5/9	0.9/ 5		/1	1.2	
КД202Н	350/500	3.5/9	0.9/ 3.5		/1	1.2	
КД202Р	420/600	5/9	0.9/ 5		/1	1.2	
КД202С	420/600	3.5/9	0.9/ 3.5		/1	1.2	
2Д202Т	560/800	3/	1/ 3		/1	1.2	
КД203А	420/600	10/30	1.0/10		/1.5	1	/20
КД203Б	560/800	5/15	1.0/ 5		/1.5	1	/20
КД203В	560/800	10/30	1.0/10		/1.5	1	/20
КД203Г	700/1000	5/15	1.0/ 5		/1.5	1	/20
КД203Д	700/1000	10/30	1.0/10		/1.5	1	/20
КД203Е	560/800	10/30	1.0/10		/1.5	1	
КД203Ж	560/800	10/30	1.0/10		/1.5	1	
КД203И	700/1000	10/	1.0/10		/1.5	1	
КД203К	700/1000	10/	1.0/10		/1.5	1	
КД203Л	280/400	10/	2.0/		/4.5	1	
КД203М	420/600	10/	2.0/		/4.5	1	
КД204А	400/400	0.4/	1.4/0.4		0.15/2	50	
КД204Б	200/200	0.6/	1.4/0.6		0.1 /1	50	
КД204В	50/ 50	1.0/	1.4/1.0		0.05/0.5	50	
КД205А	/500	0.5/	1.0/0.5		0.1/0.2	5	
КД205Б	/400	0.5/	1.0/0.5		0.1/0.2	5	
КД205В	/300	0.5/	1.0/0.5		0.1/0.2	5	
КД205Г	/200	0.5/	1.0/0.5		0.1/0.2	5	
КД205Д	/100	0.5/	1.0/0.5		0.1/0.2	5	
КД205Е	/500	0.3/	1.0/0.3		0.1/0.2	5	
КД205Ж	/600	0.5/	1.0/0.5		0.1/0.2	5	
КД205И	/700	0.3/	1.0/0.3		0.1/0.2	5	
КД205К	/100	0.7/	1.0/0.7		0.1/0.2	5	
КД205Л	/200	0.7/	1.0/0.7		0.1/0.2	5	
КД206А	400/	10/100	1.2/1		0.7/1.5	1	/10
КД206Б	500/	5/100	1.2/1		0.7/1.5	1	/10
КД206В	600/	5/100	1.2/1		0.7/1.5	1	/10
2Д207А	600/	0.5/4.5	1.5/0.5		0.15/0.5	1	0.15
КД208А	100/100	1.5/	1.0/1		0.05/0.2	1	
КД209А	400/400	0.7/15	1.0/0.7		0.1/0.3	1	
КД209Б	600/600	0.5/15	1.0/0.5		0.1/0.3	1	
КД209В	800/800	0.5/15	1.0/0.5		0.1/0.3	1	
КД209Г	1000/1000	0.2/10	1.0/0.2		0.1/0.3	1	

КД210А	800/	10/50	1.0/10		1.5/1.5	1	/20
КД210Б	800/	10/50	1.0/10		1.5/1.5	1	/20
КД210В	1000/	10/50	1.0/10		1.5/1.5	1	/20
КД210Г	1000/	10/50	1.0/10		1.5/1.5	1	/20
КД212А	200/	1/50	1.0/1	(300)	0.05/2	100	
КД212Б	200/	1/50	1.2/1	(500)	0.1/3	100	
КД212В	100/	1/50	1.0/1	(500)	0.05/2	100	
КД212Г	100/	1/50	1.2/1	(300)	0.1/3	100	
КД213А	200/200	10/100	1.0/10	(300)	0.2/10	100	
КД213Б	200/200	10/100	1.2/10	(170)	0.2/25	100	
КД213В	200/200	10/100	1.2/10	(500)	0.2/25	100	
КД213Г	100/100	10/100	1.7/10	(300)	0.2/25	100	
2Д215А	400/400	1/10	1.2/10		0.05/0.1	1	
2Д215Б	600/600	1/10	1.2/10		0.05/0.1	1	
2Д215В	200/200	1/10	1.1/10		0.05/0.1	1	
2Д216А	100/100	10/30	1.2/1		0.05/0.1	100	
2Д216Б	200/200	10/30	1.2/1		0.05/0.1	100	
2Д217А	100/100	3/9	1.1/1		0.05/2	100	
2Д217Б	100/100	3/9	1.1/1		0.05/2	100	
2Д218А	100/135	10/100	1.5/10	(300)	0.2/4	100	
2Д219А	/15	10/250	0.6/10		20/150	200	
2Д219Б	/20	10/250	0.6/10		20/150	200	
2Д220А	400/400	3/60	1.2/1	(500)	.045/1.5	10	
2Д220Б	600/600	3/60	1.2/1	(500)	.045/1.5	10	
2Д220В	800/800	3/60	1.2/1	(500)	.045/1.5	10	
2Д220Г	1000/1000	3/60	1.2/1	(500)	.045/1.5	10	
2Д220Д	400/400	3/60	1.0/1		.045/1.5	10	
2Д220Е	600/600	3/60	1.0/1		.045/1.5	10	
2Д220Ж	800/800	3/60	1.0/1		.045/1.5	10	
2Д220И	1000/1000	3/60	1.0/1		.045/1.5	10	
КД221А	/100	0.7/	1.4/0.7		0.05/0.15	50	
КД221Б	/200	0.5/	1.4/0.5		0.05/0.15	50	
КД221В	/400	/	1.4/0.3		0.1/0.3	50	
КД221Г	/600	/	1.4/0.3		0.15/0.45	20	
2Д222АС	/20	3/50	0.6/3		2/50	200	
2Д222БС	/30	3/50	0.6/3		2/50	200	
2Д222ВС	/40	3/50	0.6/3		2/50	200	
2Д222ГС	/20	3/50	0.65/3		2/50	200	
2Д222ДС	/30	3/50	0.65/3		2/50	200	
2Д222ЕС	/40	3/50	0.65/3		2/50	200	
КД223А	200/230	2/50	1.3/6		0.01/0.5	1.5	
2Д225АС	/15	3/75	0.55/3		3/30	200	
2Д225БС	/25	3/75	0.6/3		3/30	200	
2Д225ВС	/35	3/75	0.6/3		3/30	200	
КД226А	100/100	2/50	1.3/1	(250)	0.05/0.4	50	
КД226Б	200/200	2/50	1.3/1	(250)	0.05/0.4	50	
КД226В	400/400	2/50	1.3/1	(250)	0.05/0.4	50	
КД226Г	600/600	2/50	1.3/1	(250)	0.05/0.4	50	
КД226Д	800/800	2/50	1.3/1	(250)	0.05/0.4	50	
КД226Е	600/600	2/50	1.3/1	(250)	0.05/0.4	50	
КД227А	100/150	5/15	1.6/5		0.8/	1	
КД227Б	200/250	5/15	1.6/5		0.8/	1	
КД227В	300/450	5/15	1.6/5		0.8/	1	
КД227Г	400/600	5/15	1.6/5		0.8/	1	
КД227Д	500/700	5/15	1.6/5		0.8/	1	
КД227Е	600/850	5/15	1.6/5		0.8/	1	

КД227Ж	800/1200	5/15	1.6/5		0.8/	1	
2Д228А	100/100	1/50	0.15/1	(300)	.025/.25	100	
2Д229АС	/15	3/75	0.55/3		3/30	200	
2Д229БС	/25	3/75	0.6/3		3/30	200	
2Д229ВС	/35	3/75	0.6/3		3/30	200	
2Д230А	400/400	3/60	1.5/3	(500)	.045/1.5		
2Д230Б	600/600	3/60	1.5/3	(500)	.045/1.5		
2Д230В	800/800	3/60	1.5/3	(500)	.045/1.5		
2Д230Г	1000/1000	3/60	1.5/3	(500)	.045/1.5		
2Д230Д	400/400	3/60	1.3/3		.045/1.5		
2Д230Е	600/600	3/60	1.3/3		.045/1.5		
2Д230Ж	800/800	3/60	1.3/3		.045/1.5		
2Д230И	1000/1000	3/60	1.3/3		.045/1.5		
2Д231А	/150	10/150	1.0/10	(50)	0.05/2.0	200	
2Д231Б	/200	10/150	1.0/10	(50)	0.05/2.0	200	
2Д231В	/150	10/150	1.0/10	(100)	0.05/2.0	200	
2Д231Г	/200	10/150	1.0/10	(100)	0.05/2.0	200	
2Д232А	15/15	10/	0.6/10		7.5/100	200	
2Д232Б	25/25	10/	0.6/10		7.5/100	200	
2Д232В	35/35	10/	0.6/10		7.5/100	200	
2Д234А	100/100	3/	1.5/3	(400)	0.1/2.0	50	
2Д234Б	200/200	3/	1.5/3	(400)	0.1/2.0	50	
2Д234В	400/400	3/	1.5/3	(400)	0.1/2.0	50	
2Д235А	40/40	1/3	0.9/3		0.8/10		
2Д235Б	30/30	1/3	0.9/3		0.8/10		
2Д236А	600/600	1/30	1.5/1	(115)	5/	100	
2Д236Б	800/800	1/30	1.5/1	(150)	5/	100	
2Д237А	100/100	1/3	1.3/1	(50)	0.05/0.4	300	
2Д237Б	200/200	1/3	1.3/1	(50)	0.05/0.4	300	
2Д238АС	25/25	7.5/75	0.65/7.5		/1	200	
2Д238БС	35/35	7.5/75	0.65/7.5		/1	200	
2Д238ВС	45/45	7.5/75	0.65/7.5		/1	200	
2Д239А	100/100	20/80	1.4/20	(50)	0.02/	500	/25
2Д239Б	150/150	20/80	1.4/20	(50)	0.02/	500	/25
2Д239В	200/200	20/80	1.4/20	(50)	0.02/	500	/25
КД241А	1500/1500	2/5	1.4/2	(1500)	/0.005	20	3.5
КД243А	50/ 50	1/6	1.1/1		0.01/0.1	1	
КД243Б	100/100	1/6	1.1/1		0.01/0.1	1	
КД243В	200/200	1/6	1.1/1		0.01/0.1	1	
КД243Г	400/400	1/6	1.1/1		0.01/0.1	1	
КД243Д	600/600	1/6	1.1/1		0.01/0.1	1	
КД243Е	800/800	1/6	1.1/1		0.01/0.1	1	
КД243Ж	1000/1000	1/6	1.1/1		0.01/0.1	1	
КД244А	100/100	10/100	1.3/10	(50)	0.1/	200	
КД244Б	100/100	10/100	1.3/10	(35)	0.1/	200	
КД244В	200/200	10/100	1.3/10	(50)	0.1/	200	
КД244Г	200/200	10/100	1.3/10	(35)	0.1/	200	
2Д245А	400/450	10/100	1.4/10	(70)	0.1/	200	/20
2Д245Б	200/250	10/100	1.4/10	(70)	0.1/	200	/20
2Д245В	100/150	10/100	1.4/10	(70)	0.1/	200	/20
КД247А	100/100	1/30	1.3/1	(150)	/0.1	150	
КД247Б	200/200	1/30	1.3/1	(150)	/0.1	150	
КД247В	400/400	1/30	1.3/1	(150)	/0.1	150	
КД247Г	600/600	1/30	1.3/1	(150)	/0.1	150	
КД247Д	800/800	1/30	1.3/1	(250)	/0.1	150	

КД247Е	50/50	1/30	1.3/1	(150)	/0.1	150	
КД248А	1000/1000	3/9.6	1.4/3	(250)	/1	100	2.5
КД248Б	1000/1000	1/3.2	1.4/1	(250)	/1	100	2
КД248В	800/800	3/9.6	1.4/3	(250)	/1	100	4.5
КД248Г	800/800	1/3.2	1.4/1	(250)	/1	100	2
КД248Д	600/600	3/9.6	1.4/3	(250)	/1	100	4.5
КД248Е	600/600	1/3.2	1.4/1	(250)	/1	100	2
КД248Ж	400/400	3/9.6	1.4/3	(250)	/1	100	2.5
КД248И	400/400	1/3.2	1.4/1	(250)	/1	100	2
КД248К	1000/1200	1.5/4.8	1.1/1.5	(250)	/1	65	2.5
2Д249А	40/40	3/10	0.475/3	750/1	/3		2.5
2Д249Б	30/30	3/10	0.475/3	750/1	/3		2.5
2Д249В	20/20	3/10	0.475/3	750/1	/3		2.5
2Д250А	125/140	10/40	1.4/10	55/100	0.05/	100	