

Rittal – The System.

Faster – better – everywhere.

Switch housings Stainless steel – SM 2384.040

Date : Apr 27, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Switch housings Stainless steel – SM 2384.040

created: 27.04.2021 build on www.rittal.com/uk-en



Product description

Material: Enclosure: Stainless steel 1.4301 (AISI 304)
Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal

Surface finish: Enclosure and cover: Brushed, grain 240

**Protection category
IP to IEC 60 529:** IP 66

**Protection category
NEMA:** NEMA 4X

Supply includes: Enclosure with cover
Quick-release fastener including plastic bushes

Basic material: Stainless steel

Product description

Dimensions: Width: 280 mm
Height: 100 mm
Depth: 90 mm

Pitch pattern: 60 mm

Material thickness: Enclosure: 1.25 mm
Cover: 1.25 mm

**No. of switch cut-outs
Ø 22.5 mm:** 4

Lock version: Quick-release fastener including plastic bushes

Number of locks:	4
Packs of:	1 pc(s).
Weight/pack:	1.1 kg
EAN:	4028177529441
Customs tariff number:	94039010
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	SM Switch housing, WHD: 280x100x90 mm, Stainless steel 1.4301, without mounting plate, 4 switch cut-outs
Approvals	
Approvals:	RRR
Certificates:	EAC NA
Declarations:	Declaration of conformity