
quick exhaust valve SEU-1/8 Part number: 4616

SEU-1/8
Part number: 4616

With built-in silencer.

The exhaust noise level is measured at 6 bar to atmosphere at 1 m distance.





| Feature | Value |
|--|---|
| Valve function | Quick exhaust |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Mounting type | Threaded |
| Standard nominal flow rate, exhaust | 550 l/min |
| Standard flow rate for exhaust 6->0 bar | 1,000 l/min |
| Standard nominal flow rate for pressurisation 6->5 bar | 300 l/min |
| Operating pressure | 0.5 10 bar |
| Ambient temperature | -20 75 °C |
| Material housing | Zinc die-casting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Nominal size | 5 mm |
| Assembly position | Any |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Medium temperature | -20 75 °C |
| Sound pressure level | 85 dB(A) |
| Product weight | 65 g |
| Material seals | NBR |