



Fuse-link, LV, 6 A, AC 240 V, BS88, 15 x 49 mm, gL/gG, BS

Catalog No. LST6

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	6
Rated voltage			AC 240 V
Construction size			BS88
Size			15 x 49 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			street lighting cut-outs
Standard/Approval			BS
Shape			offset bolted tags (slotted)
Standards/Regulations			BS88 IEC 60269

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	6
Rated voltage		V	240
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No