

## FEATURES

- The body is available in burnished steel with black oxide finish or stainless steel
- Hardened plunger
- Knob material – high impact resistant thermoplastic
- Knob finish – matt
- Standard colour – black knob
- Comes at standard with 90° locking rest position in plunger body

## RS PRO M12 Index Plunger, 61mm Long

RS Stock No.: 478-721



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description ATTRIBUTE

These spring-loaded hand retractable plungers from our own RS PRO brand are designed to prevent any change in locking position due to lateral force. Pulling up on the handle retracts the plunger pin into the body.

## General Specifications


<b>Type</b>	Index Plunger
<b>Body Material</b>	Burnished steel
<b>Thread Size</b>	M12
<b>Applications</b>	Clamping of adjustable elements, Positioning of work pieces, Latching of mechanisms
<b>Rest Position</b>	No

## Mechanical Specifications

<b>Length</b>	61mm
<b>Ball Diameter</b>	6mm

## Approvals

<b>Compliance/Certifications</b>	RoHS
----------------------------------	------



Part No.	A	B	C	D	E	Thread size	Plunger diameter (mm)	Rest position
478359	21	51	5	17	5	M10x1.0	5	No
237491	25	45	5	10	6	M12x1.5	6	No
478721	25	61	6	20	6	M12x1.5	6	No
237429	31	54	6	12	8	M16x1.5	8	No
478769	31	75	8	26	7	M16x1.5	8	No
237570	25	45	5	10	6	M12x1.5	6	Yes
237388	31	54	6	12	8	M16x1.5	8	Yes