


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA13-A THRU PCA13-Z	'A' THRU 'Z'	30	300	1	10	.130"-.150"
PCA13-A-J	'A'-'J' [1 EA.]	30	300	1	10	.130"-.150"
PCA13-K-T	'K'-'T' [1 EA.]	30	300	1	10	.130"-.150"
PCA13-U-Z	'U'-'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.130"-.150"
PCA13-0 THRU PCA13-9	'0' THRU '9'	30	300	1	10	.130"-.150"
PCA13-0-9	'0'-'9' [3 EA.]	30	300	1	10	.130"-.150"
PCA13-MIN	'-'	30	300	1	10	.130"-.150"
PCA13-PLS	'+'	30	300	1	10	.130"-.150"

NOTES:

- COLOR: WHITE WITH BLACK LEGENDS.
- MILLIMETERS ARE IN [],
- TWO SIDES PRINTED.



5

5

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	10/27/15	RVU	SEWH	JHAC	ADD NOTE 3 TO SHOW TWO SIDES PRINTED.	GAECN03227
4	4/22/13	RVU	SEWH	JHAC	CHANGE OLD DRAWING BOARDER TO NEW PANDUIT DRAWING BOARDER.	GAECN02989
3	3/28/11	RVU			ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336
2	8/11/10	RVU			UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT. UPDATE TABLE.	6079
1	7/15/07	RVU			ADDED TOLERANCE AND REVISED TABLE.	4981
0	10/5/06	RVU			DRAWING RELEASE.	4715

TITLE		PCA13-* CLIP-ON WIRE MARKER		
ITEM REVISION NAME		CUSTOMER DRAWING		
DATASET FILE NAME		I00281DF/06		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT MATERIAL: WHITE MARKER-ACETAL		
.x ± .12 [3.05] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ±				
DRAWN BY		DATE	CHK	SCALE
RVU		9/5/04	JM	NTS
DRAWING NUMBER:		C10346		
SHT 1 OF 1		A		

D10100DA/15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCA13-K-T](#) [PCA13-0-9](#) [PCA13-1](#) [PCA13-2](#) [PCA13-3](#) [PCA13-8](#) [PCA13-5](#) [PCA13-D](#) [PCA13-U](#) [PCA13-A-J](#)
[PCA13-R](#) [PCA13-W](#) [PCA13-P](#) [PCA13-9](#) [PCA13-MIN](#) [PCA13-6](#) [PCA13-S](#) [PCA13-PLS](#) [PCA13-B](#) [PCA13-4](#)
[PCA13-O](#) [PCA13-H](#) [PCA13-I](#) [PCA13-X](#) [PCA13-Q](#) [PCA13-A](#) [PCA13-C](#) [PCA13-0](#) [PCA13-E](#) [PCA13-Y](#) [PCA13-7](#)
[PCA13-K](#) [PCA13-V](#) [PCA13-F](#) [PCA13-T](#) [PCA13-G](#) [PCA13-N](#) [PCA13-J](#) [PCA13-Z](#) [PCA13-L](#) [PCA13-M](#) [PCA13-U-Z](#)