



Fuse-link, low voltage, 315 A, AC 660 V, DC 460 V, 80 kA, BS88/B3, 53 x 137 mm, gM, BS, motor-rated

Part no. 315M355A 660V AC / 460V DC BS88 FUSE
Catalog No. TKF315M355

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	315
Motor current rating	I	A	315M355
Rated voltage			AC 660 V DC 460 V
Construction size			BS88/B3
Size			53 x 137 mm
Utilization category			gM
Description			motor-rated
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			centre-bolted tags
Standards/Regulations			BS88-2 IEC 60269-2

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	315
Rated voltage		V	660
Voltage type			AC/DC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No