

领亚电子科技股份有限公司

No.2, The
Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China
Tel:(86)-769-85550688 Fax:(86)-769-85550388

承 认 书

SPECIFICATION FOR APPROVAL

产 品: SFTP CAT. 5e 24AWG×4P AS

PRODUCT

料 号: _____

PART NO.

客户名称: Chipdip

CUSTOMER

承认书编号: TX-026A0602-A

SHEET NO.

客户 料号: _____

CUSTOMER NO.

UL/CSA STANDARD: _____

Non-standard: _____

日 期: 2019-6-19

DATE:

CUSTOMER CONCLUSION: APPROVED (承认)

(客户判定)

LIMIED (允收)

REJECT (拒收)

CONDITIONAL APPROVAL (条件认可)

INCLUDING THIS COVER TOTAL 3 PAGES

(含封面页共 3 页)

* PLEASE SIGNED AND FAX THE RESULT TO US.

(请于判定签名后将结果传回)

AUTHORIZED SIGNATURES

领亚电子科技股份有限公司

No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China

Tel:(86)-769-85550688

Fax:(86)-769-85550388

CABLE SPECIFICATION(线材承认书)

SPEC NO.	TX-026A0602		PART NO.	
UL FILE NO.		UL STYLE		NON-STANDARD
CSA FILE NO.		CSA STYLE		版本 A
CONSTRUCTION ITEM/ 结构项目		结构项目		
CONDUCTOR 导体	CONSTRUCTION 构造规格	AWG	7/0.160±0.008	
	MATERIAL/导体材质	-----	BARE STRAND COPPER CONDUCTOR	
INSULATION 绝缘	MATERIAL/材质	-----	HDPE	
	OD / 芯线外径	mm	0.95±0.1	
	AVERAGE THICKNESS 平均厚度	mm	0.23(REF)	
	COLOR / 颜色	-----	1P. WHITE&BROWN 2P. WHITE&BLUE 3P. WHITE&ORANGE 4P. WHITE&GREEN	
INNET-ASSEMBLE 内集合	OD/绞合外径	mm	4.28 (REF)	
INSIDE-TAPE WRAP 内部包装	MATERIAL/包带材质	-----	MYLAR	
	CONDUCTIVE/导电面	-----	---	
	OVERLAP RATE/重叠率	%	25%	
DRAIN WIRE 地 线	CONSTRUCTIO/构造	mm	1/0.404±0.007	
	MATERIAL/导体材质	-----	COPPER COVER STEEL	
OUTSIDE-SHIELD 外部遮蔽	MATERIAL/包带材质	-----	AL-MYLAR	
	CONDUCTIVE/导电面	mm	OUTSIDE	
	OVERLAP RATE/重叠率	-----	25%	
WEAVING 编织	CONSTRUCTION 构造规格	mm	8/4/0.12±0.007	
	MATERIAL/导体材质	-----	ALUMINIUM MAGNESIUM ALLOY WIRE	
JACKET 外被 MARKING 喷字	MATERIAL/材质	-----	PVC	
	DIAMETER/线径	mm	6.3±0.2	
	AVERAGE THICKNESS 平均厚度	mm	0.6(REF)	
	COLOR/颜色	-----	GREY PANTONE cool gray 5C	
	MARKING COLOR/ 喷字颜色	-----	BALCK	
	JACKET 外被	-----	LAN CABLE SFTP CAT.5E 24AWG 4PAIRS EIA/TIA-568B ***M (001M-305M)	

LY-QPM-FOR-053 A/0

领亚电子科技股份有限公司

No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China

Tel:(86)-769-85550688

Fax:(86)-769-85550388

CABLE SPECIFICATION(线材承认书)

SPEC NO.	TX-026A0602		PART NO.		
UL FILE NO.		UL STYLE		NON-STANDARD	
CSA FILE NO.		CSA STYLE		版本	A

Electric characters

- 1.Voltage rating(额定电压) 30V
- 2.Temperature rating(额定温度) 75°C
- 3.Spark test(火花测试) 1.5KV
- 4.Dielectric strength(耐压强度) AC-500V/MIN
- 5.Insulation resistance(绝缘电阻) 100 M OHM/KM MIN at 20°C


Physical Characters

- 1.Tensile strength before aging(老化前抗张强度测试)
 - 1.1 Jacket : >1.05kg/mm²
- 2.Elongating before aging (老化前断裂伸长率)
 - 2.1 Jacket : > 100%

Environmental requirements: 1. 不含双方签订的环保标准的 1 级管理物质

Cross drawing:

截面示意图



APPROVER		CHECK		DESIGNER	LLL
----------	--	-------	--	----------	-----