

领亚电子科技股份有限公司

No.2, The
Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China
Tel:(86)-769-85550688 Fax:(86)-769-85550388

承 认 书

SPECIFICATION FOR APPROVAL

产 品: UTP CAT. 5e 24AWG×4P SOLID

PRODUCT

料 号: _____

承认书编号: TX-024A0645-A

PART NO.

SHEET NO.

客户名称: Chipdip

客户 料号: _____

CUSTOMER

CUSTOMER NO.

UL/CSA STANDARD: _____

Non-standard: _____

日 期: 2019-6-19

DATE:

CUSTOMER CONCLUSION: APPROVED (承认)

(客户判定)

LIMIED (允收)

REJECT (拒收)

CONDITIONAL APPROVAL (条件认可)

INCLUDING THIS COVER TOTAL 3 PAGES

(含封面页共 3 页)

* PLEASE SIGNED AND FAX THE RESULT TO US.

(请于判定签名后将结果传回)

AUTHORIZED SIGNATURES

领亚电子科技有限公司

No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China

Tel:(86)-769-85550688

Fax:(86)-769-85550388

CABLE SPECIFICATION(线材承认书)

SPEC NO.	TX-024A0645		PART NO.	
UL FILE NO.		UL STYLE		NON-STANDARD
CSA FILE NO.		CSA STYLE		版本 A
CONSTRUCTION ITEM/ 结构项目		结构项目		
CONDUCTOR 导体	CONSTRUCTION 构造规格	AWG	1/0.500±0.005	
	MATERIAL/导体材质	-----	BARE SOLID COPPER CONDUCTOR	
INSULATION 绝缘	MATERIAL/材质	-----	HDPE	
	OD / 芯线外径	mm	0.88±0.10	
	AVERAGE THICKNESS 平均厚度	mm	0.19(REF)	
	COLOR / 颜色	-----	1P. BROWN & WHITE / BROWN 2P. BLUE & WHITE / BLUE 3P. ORANGE & WHITE / ORANGE 4P. GREEN & WHITE / GREEN	
FILLER 填充	MATERIAL/材质	-----	RIP CORD	
	CONSTRUCTION/构造	%	3*250D	
OUTSIDE-TAPE WRAP 外部包装	MATERIAL/包带材质	-----	/	
	CONDUCTIVE/导电面	-----	/	
	OVERLAP RATE/重叠率	%	/	
OUTSIDE-SHIELD 外部遮蔽	MATERIAL/包带材质	-----	/	
	CONDUCTIVE/导电面	-----	/	
	OVERLAP RATE/重叠率	%	/	
INNER-ASSEMBLE 内集合	OD/绞合外径	mm	3.9(REF)	
JACKET 外被	MATERIAL/材质	-----	PVC	
	DIAMETER/线径	mm	4.9±0.3	
	AVERAGE THICKNESS 平均厚度	mm	0.50(REF)±0.05	
	COLOR/颜色	-----	GREY PANTONE cool gray 5C	
	MARKING COLOR/ 喷字颜色	-----	BLACK	
MARKING 喷字	JACKET 外被	-----	LAN CABLE UTP CAT.5E 24AWG 4PAIRS SOLID ***M (001M-305M)	

<p>领亚电子科技股份有限公司</p> <p>No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone, Songshan Lake, Dongguan City, Guangdong Province, China</p> <p>Tel:(86)-769-85550688 Fax:(86)-769-85550388</p> <p>CABLE SPECIFICATION(线材承认书)</p>					
SPEC NO.	TX-024A0645	PART NO.			
UL FILE NO.		UL STYLE		NON-STANDARD	
CSA FILE NO.		CSA STYLE		版本	A
<p>Electric characters</p> <p>1.Voltage rating(额定电压) 30V</p> <p>2.Temperature rating(额定温度) 75°C</p> <p>3.Dielectric strength(耐压强度) AC-500V/MIN</p> <p>4.Insulation resistance(绝缘电阻) 100 M OHMS.KM MIN at 20°C</p>					
<p>Physical Characters</p> <p>1.Tensile strength before aging(老化前抗张强度测试)</p> <p style="padding-left: 20px;">1.1 Jacket : >1.05kg/mm²</p> <p>2.Elongating before aging (老化前断裂伸长率)</p> <p style="padding-left: 20px;">2.1 Jacket : > 100%</p>					
<p>Environmental requirements: 1. 不含双方签订的环保标准的 1 级管理物质</p>					
<p>Cross drawing: 截面示意图</p> <div style="text-align: center;"> <p>The diagram shows a circular cross-section of a cable. It features four pairs of conductors arranged in a 2x2 grid, labeled 1P, 2P, 3P, and 4P. Each pair consists of two conductors of different diameters. The conductors are surrounded by an insulation layer. A small circular feature, labeled 'RIP CORD', is located between the conductor pairs. The entire assembly is enclosed within an outer 'JACKET' layer.</p> </div>					
APPROVER		CHECK		DESIGNER	LLL