

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [52044-1445](#)
Status: **Active**
Overview: [FFC-FPC \(Through-Hole\)](#)
Description: FFC/FPC Connector, Non-ZIF, Right-Angle, Top Contact Style Receptacle, 14 Circuits

Documents:

[3D Model](#) [Product Specification PS-52044-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family FFC/FPC Connectors
 Series [52044](#)
 Overview [FFC-FPC \(Through-Hole\)](#)
 Product Name N/A
 UPC 800753572706

Physical

Circuits (Loaded) 14
 Contact Position Top
 Entry Angle 90° Angle
 Flammability 94V-0
 Mated Height 5.10mm
 Net Weight 1247.600/mg
 Number of Rows 1
 Orientation Right Angle
 PC Tail Length 3.50mm
 PCB Retention None
 Packaging Type Tray
 Pitch - Mating Interface 1.25mm
 Polarized to PCB Yes
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40°C to +85°C
 Termination Interface: Style Through Hole
 Wire/Cable Type FFC/FPC

Electrical

Current - Maximum per Contact 0.5A, 1A
 Voltage - Maximum 200V

Material Info

Reference - Drawing Numbers

Product Specification PS-52044-002, RPS-52044-003, RPS-52044-005,
 RPS-52044-006, RPS-52044-008
 Sales Drawing SD-52044-**45




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[52044Series](#)