



**PCB TERMINAL STRIP 1 SOLDER PIN  
/ POLE STAGGERED PIN SPACING 3.5  
MM / 0.138 IN WITH PUSH BOTTONS  
WITH TEST SLOT FOR Ø  
805-102 TO 805-124**

<b>ITEM-NO. (ITEM-NO.)</b>	805-104
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.2 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	24 - 16
<b>Strip length (Strip length / mm)</b>	9 - 10
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	17.5
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	4
<b>Height (Height / mm)</b>	10.5
<b>Width (Width / mm)</b>	16.1
<b>Depth (Depth / mm)</b>	13.6
<b>No. of connection Points (No. of connection Points)</b>	4
<b>No. of potentials (No. of potentials)</b>	4
<b>COLOR (COLOR)</b>	grau
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 1,5 mm + 0,6 mm
<b>Dimensions (Dimensions)</b>	1.1+0,1 mm