



Quality Products. Service Excellence.

Rack Mount Basic PDU *1582E Series*

10A | Single-Phase 100-240V | Front or Rear Facing C13 Outlets

Features



- Rated 100-240VAC (TUV), 120-240VAC (UL), 10A, 50/60Hz
- Designed for power distribution on front or rear of unit with IEC power cords.
- 1U horizontal 19" rackmount installation.
- All steel housing with black powder coat finish.
- On-Off switch is rocker type with green light (on those units with on-off switch) or a green pilot light to indicate power on.

Specifications

- Includes 10A circuit breaker to prevent accidental line overload.
- cULus Listed UL 62368-1 (2nd Edition), 2014-12-01, and CAN/CSA C22.2 No. 62368-1-14 (2nd Edition).
- TÜV-SUD Certified to EN 62368-1:2014/A11:2017, and IEC 62368-1:2014 (2nd Edition)
- TÜV-SUD tested for EMC Compliance to EN 55032:2012 (CISPR 32:2012) & EN 55024:2010 (CISPR 24:2010).
- CE compliant to the European Low Voltage Directive 2014/35/EU.
- CE compliant to the European EMC Directive 2014/30/EU.



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit
- Input Accessory Cords

With Illuminated On/Off Switch Part No.	Pilot Light Only Part No.	Overall Dimensions			Number of Outlets		Outlet Type	Inlet Type	Inlet Location
		Height	Width	Depth	Front	Rear			
1582H8E1BK	1582T8E1BK	1.72	19.00	2.66	8	0	C13	C14	Rear
1583H8E1BK	1583T8E1BK	1.72	19.00	2.66	0	8	C13	C14	Rear

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1583T8E1BK](#) [1582T8E1BK](#) [1582H8E1BK](#) [1583H8E1BK](#)