



# 1050QC, 1051QC, 1052QC, 1053QC and 1090QC Series Non-Relampable Neon-Incandescent Indicator Lights



Mounting: Will snap-fit into Ø.500/.505 hole in panels .020/.100 thick. Push-on speednut SN0461 also available.

Terminals: Tinned brass

Lens: Polycarbonate

Bezel: Polished stainless steel.

Housing: White Nylon

| Lens Color | Neon                   |                      | Incandescent    |                 |
|------------|------------------------|----------------------|-----------------|-----------------|
|            | Model No. (105-125VAC) | Model No. (208-250V) | Model No. (12V) | Model No. (28V) |
| Red        | 1050QC 1               | 1051QC 1             | 1090QC 1-12V    | 1090QC 1-28V    |
| Clear      | 1050QC 2               | -                    | -               | -               |
| Amber      | 1050QC 3               | 1051QC 3             | -               | 1090QC3-28V     |
| White      | 1050QC 4               | 1051QC 4             | 1090QC 4-12V    | 1090QC4-28V     |
| Green      | 1052QC 5*              | 1053QC 5*            | 1090QC 5-12V    | 1090QC5-28V     |
| Lamp used  | C 2A+R resistor        | C 2A+R resistor      | #2162           | #2187           |

\* Incorporates G2B lamp and resistor.  
Underwriters Laboratories (UL) File No. E20356

## Compliance & Approvals



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[1053QC5](#) [1090QC1-28V](#) [1090QC1-12V](#) [1051QC3](#) [1051QC1](#) [1090QC3-28V](#) [1052QC5](#) [1050QC4](#) [1050QC2](#)  
[1050QC3](#) [1050QC1](#) [1090QC5-28V](#) [1090QC4-28V](#) [1090QCX1-28V](#) [1051QC4](#)