

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430238](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: [Watertite Extreme Cordset, 12 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 15.24m \(50.0'\), NEMA L14-20, 250V](#)

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family [Wiring Devices](#)
 Series [130143](#)
 IP Rating IP67
 NEMA Configuration NEMA L14-20
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type Single
 Specialty N/A
 Type Cordset
 UPC 78678871256

Physical

Cord Grip Body Size F3 3/4"
 Flange No
 Flip Lid No
 Gender Male-Female
 Length 15.24m (50.0')
 Locking Blade Yes
 Net Weight 5485.000/g
 Poles 3-pole/4-wire

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 20.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 250V

Material Info

Engineering Number 26W74B124



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130143 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301430129](#) [1301460050](#) [1301460054](#) [1301460077](#)